

## WheelAir Cooling Backrest



- By dispersing air evenly across your back using the patented channel technology, it helps avoid symptoms caused by overheating and over sweating while keeping skin dry and clean.
- Through active airflow, WheelAir allows for self regulation of the body temperature through convection, conduction and evaporation heat loss.
- 7-20 hours of battery life depending on setting
- Charges in 17 Hours from dead to full (overnight).
- 4 fan setting controlled by remote discretely attached to backrest



### Warranty Information

- 1 Year

WheelAir

| Code      | Display Name                      | Total Height | Safe Working Load | Backrest Height | Backrest Width |
|-----------|-----------------------------------|--------------|-------------------|-----------------|----------------|
| PTB541100 | WheelAir Cooling Backrest - 290mm | 740 mm       | 130 kg            | 300 - 450 mm    | 290 mm         |
| PTB541110 | WheelAir Cooling Backrest - 330mm | 740 mm       | 130 kg            | 300 - 450 mm    | 330 mm         |
| PTB541120 | WheelAir Cooling Backrest - 360mm | 740 mm       | 130 kg            | 300 - 450 mm    | 360 mm         |
| PTB541130 | WheelAir Cooling Backrest - 400mm | 740 mm       | 130 kg            | 300 - 450 mm    | 400 mm         |
| PTB541140 | WheelAir Cooling Backrest - 420mm | 740 mm       | 130 kg            | 300 - 450 mm    | 420 mm         |