

Aspire Evoke 2 Wheelchair





- The Evoke 2 is designed for the user who wants a lightweight, highly adjustable manual wheelchair.
- The Contoured Padded Overlay (shown in image #2) is a stylish
 recommended accessory for the Aspire Evoke 2. The contoured padded
 overlay offers the user increased comfort and is ideal for those who are in
 their wheelchair for longer periods of time. The mild contouring assists in
 positioning and pressure distribution, while the fabric allows air movement,
 increasing breathability. It is easily removed to allow washing when required
- Swing-in / out, height adjustable and removable foot rests this facilitates user transfers and allows optimal positioning for the changing needs
- Strong, Nylon upholstery with a comfortable cushion and padded backrest. For increased comfort, a padded overlay is available as an accessory.
- Depth adjustable seating with rear angle adjustability for more accurate positioning, customisability and increased user comfort.
- Quick release 24" solid rear tyres the wheels are easily removed to reduce the weight of the chair for transport and storage./li>
- Crash Tested to AS/NZ3616.196

Warranty Information

- 2 Years Frame
- 1 Year Components

- Contracted DVA productZ
- Ocontract approved

ndis

Item Code:

05_122203104_0105_1_2

Wheelchair Manual - Composite:

05_417_0105_1_2

Click here for more information

Accessories

Click on the cart icon to display the range of optional accessories

Code	Display Name	Seat Depth	Seat Width	Backrest Height	Seat To Floor Height	Safe Working Load	Unit Weight	Colour	Material
MWS449500	Aspire Evoke 2 - 350mm Wide	400 - 475 mm	350 mm	430 - 490 mm	440 - 480 mm	140 kg	14.8 kg	Silver	Aluminium



Code	Display Name	Seat Depth	Seat Width	Backrest Height	Seat To Floor Height	Safe Working Load	Unit Weight	Colour	Material
MWS449510	Aspire Evoke 2 - 400mm Wide	400 - 475 mm	400 mm	430 - 490 mm	440 - 480 mm	140 kg	14.9 kg	Silver	Aluminiur
MWS449520	Aspire Evoke 2 - 450mm Wide	400 - 475 mm	450 mm	430 - 490 mm	440 - 480 mm	140 kg	15.0 kg	Silver	Aluminiun
MWS449530	Aspire Evoke 2 - 500mm Wide	400 - 475 mm	500 mm	430 - 490 mm	440 - 480 mm	140 kg	15.1 kg	Silver	Aluminiun