



NSW HEALTH CF820

CLINICAL FURNITURE & EQUIPMENT CATALOGUE

NOVEMBER 2019

VERSION: 1 | CREATED NOVEMBER 2019





Aidacare

Aidacare are proud to be recognised as a NSW HealthShare / EnableNSW contracted service provider for a large range of products included in the recently announced **Clinical Furniture** contract. Our commitment to NSW HealthShare stakeholders, including prescribing healthcare professionals NSW HealthShare client, is to provide the best of services and product quality available.

For the healthcare prescriber, Aidacare offer industry leading support to assist in the provision of equipment for your clients.

- Most contracted products are available for viewing, in-home assessment or trial, anywhere in New South Wales, to determine suitability for the facility or client's specific needs. Our equipment consultants can meet at any location, including client's private homes, to demonstrate items.
- Display stock is available at each of the Aidacare showrooms to enable prescribers to meet with clients on-site to view and assess all required items in a professional environment.
- Many Aidacare showrooms also offer prescribers use of a private office and meeting room to utilise while meeting with clients or just to catch up on admin and reports.
- Specialist Complex Rehab & Seating staff are available to assist with prescription of customised and specialised equipment.
- Clinical education and support is also available via the Aidacare Professional Training program and workshops.
- Service and repair of all contracted items is conducted by our workshop and mobile technicians.
- The Customer Service Team is available for additional support, including booking for product viewing, general advice and information as required.

Our electronic catalogue is available for download at www.aidacare.com.au/globalassets/resources

For information on any of the extensive range of products available from Aidacare, please browse the complete online Aidacare catalogue at www.aidacare.com.au

For additional information, please contact your local Aidacare office directly on **1300 133 120** or email nswhealth@aidacare.com.au

NSW Healthshare & Enable NSW

EnableNSW provides equipment and services to people in NSW with chronic health conditions or disability to assist them with mobility, communication and self-care. They also provide assistance for people who need to travel significant distances for specialist medical care.

AIDS AND EQUIPMENT PROGRAM

The Aids and Equipment Program is a NSW Government initiative to assist eligible residents of NSW, who have a life-long or long-term disability, to live and participate within their community, by providing appropriate equipment, aids and appliances.

Information on eligibility for the program, the range of equipment available, the lodgement of applications, mutual responsibilities and expectations, and steps for complaints and appeals is outlined in the Policy Directive - "Assistive Technology for Communication, Mobility, Respiratory Function & Self-Care." https://www1.health.nsw.gov.au/PDS/pages/doc.aspx?dn=PD2011_027


People with a disability interested in seeking further information about the program should discuss their query with a healthcare provider, or Enable NSW on **1800 ENABLE (1800 362 253)**

As part of HealthShare NSW, EnableNSW is responsible for the administration of NSW Health disability support and other assistance programs including:

- Aids and Equipment Program
- Continence Assistance
- Home Respiratory Program (HRP)
- Prosthetic Limb Service (formerly known as ALS)
- Specialised Equipment Essential for Discharge (SEED)

For more information, visit the EnableNSW website: <http://www.enable.health.nsw.gov.au/>


State Wide Distribution Network

 **MOOREBANK**
3A / 1 Moorebank Ave,
Moorebank NSW 2170
Tel: (02) 8706 2300
Fax: (02) 9618 5111

 **SEVEN HILLS**
2/4 Stanton Rd,
Seven Hills NSW 2147
Tel: (02) 8706 2330
Fax: (02) 9624 4256

 **BLACKTOWN**
1/34 Campbell St
Blacktown NSW 2178
Tel: (02) 9621 4077


 **WOLLONGONG**
140 Church St
Wollongong NSW 2500
Tel: (02) 8706 2359


 **ALBURY**
347 Urana Rd,
Lavington NSW 2641
Tel: (02) 6040 3444
Fax: (02) 6040 3222

 **BALLINA**
18 Endeavour Close,
Ballina NSW 2478
Tel: (02) 6686 6644
Fax: (02) 6686 9383

 **COFFS HARBOUR**
2/177 Orlando St,
Coffs Harbour NSW 2450
Tel: (02) 6651 5333
Fax: (02) 6652 1272

 **PORT MACQUARIE**
1/171 Lake Rd,
Port Macquarie NSW 2444
Tel: (02) 6581 0018
Fax: (02) 6581 0038

 **ORANGE**
Unit 1, 12-16 Ash St,
Orange NSW 2800
Tel: 0437 134 295

 **TAMWORTH**
3/248 Peel St,
Tamworth NSW 2340
Tel: (02) 6761 2018
Fax: (02) 6761 2090



CALL 1300 133 120

Call this number to be automatically diverted to your local Aidacare office (for the price of a local call).



Product Index

Bathroom & Toilet p 4

Shower Commodes	4
Shower Commode Accessories	5
Shower Seating	6
Bath Seating	6
Shower Trolleys	6

Bedroom p 7

Overbed Tables	7
Bed Cradles	7
Bedside Commode	7
Bedside Cabinet	8

Chairs p 9

Powerlift Recline Chairs	9
Therapeutic Recline Chairs	11
Day Chairs	12

Hospital & Ward Equipment p 14

General Ward Equipment	14
Instrument/Dressing Trolleys	15

Cushions & Seating p 16

Pressure Care Cushions	16
Cushion Covers	18

Manual Handling - Lifters & Slings p 19

Aspire Patient Lifters	19
Aspire Patient Slings	21
Liko Patient Lifters	22
Liko Patient Slings	23
Ceiling Hoists	24

Manual Handling - Other p 26

Transfer Boards & Sheets	26
Transfer & Walk Aids	27

Linen Skips p 28

Linen Skips	28
Linen Skip Accessories	29
Linen Bags	29

Ramps p 30

Ramps	30
-------------	----

Mobility Wheelchairs & Positioning p 31

Manual Wheelchairs	31
Power Wheelchairs	45
Wheelchair Accessories	59
Wheelchair Backrests	61

Paediatric p 64

Strollers	64
-----------------	----



Bathroom & Toilet



Shower Commodes

Description	Code	Image
-------------	------	-------

Aspire Shower Commodes

Aspire Bariatric - SA Footrest - 790mm - 350kg (seat incl)	BTC061200	
Aspire - SA Footrest - 600mm - Stainless Steel - (seat sep) - 200kg	BTC061300	
Aspire - Self Prop - SA Footrest - 600mm - Stainless Steel (seat sep) - 200kg	BTC061305	
Aspire - WB Platform - 600mm - Stainless Steel (seat sep) - 400kg	BTC061400	
Aspire - SA Footrest - 460mm - Stainless Steel (seat sep) - 200kg	BTC065900	
Aspire - WB Platform - 460mm - S/Steel (seat sep) - Stainless Steel Castors & Safety Arms - 200kg	BTC066000	

Shower Commodes

Description	Code	Image
-------------	------	-------

Aspire - Tilt & Recline - 460mm - Height Adj - Stainless Steel (seat sep) - 250kg	BTC066030	
Aspire - Tilt & Recline - 530mm - Height Adj - Stainless Steel (seat sep) - 250kg	BTC066040	
Aspire - WB Platform - 530mm - Stainless Steel (seat sep) - 200kg	BTC066050	
Aspire - Self Prop - WB Platform - 530mm - Stainless Steel (seat sep) - 200kg	BTC066055	
Aspire - SA Footrest - 530mm - Stainless Steel (seat sep) - 200kg	BTC066060	
Aspire - Self Prop - SA Footrest - 530mm - Stainless Steel (seat sep) - 200kg	BTC066065	



Shower Commodes

Description	Code	Image
Aspire - Self Prop - SA Footrest - 460mm (seat sep) - 200kg CHP198955 CHP198955 CHP198955	BTC066100	
Aspire - Self Prop - WB Platform - 460mm (seat sep) - 200kg	BTC066200	
Aspire - Aluminium Att Prop - 440mm (seat incl) - 136kg	BTC068010	
Aspire - Aluminium Self Prop - 440mm (seat incl) - 136kg	BTC068020	

Verto Shower Commodes

Verto - Height Adj - Att Prop w/ Swing Away Footrest - 550mm (seat sep)	BTC069450	
Verto - Self Prop w/ Swing Away Footrest - 550mm (seat sep)	BTC069460	
4HC - Tilt in Space - Att Prop w/ Swing Away Footrest - 550mm (seat sep)	BTC069470	
4HC - Self Prop w/Swing Away Footrest (seat sep)	BTC069480	
Verto- Height Adj - Att Prop w/ Swing Away Footrest - 475mm (seat sep)	BTC069490	
4HC - Att Prop w/Platform Footrest (seat sep)	BTC069495	
4HC - Tilt in Space - Att Prop w/ Swing Away Footrest - 545mm (seat sep)	BTC069500	

Shower Commode Accessories

Description	Code	Image
Bowl & Pan Carrier - Aspire Shower Commodes - 460/530/600mm	BTC066400	
Oxygen Bottle Carrier - Aspire Shower Commodes	BTC067200	
Pelvic Strap - Adjustable - Aspire Shower Commodes	BTC067100	

Aspire Shower Commode Seats

Closed 410mm	BTC066500	
Open 460mm	BTC066600	
Closed 460mm	BTC066700	
Open 530mm	BTC066750	
Open 600mm	BTC066800	

Aspire Shower Commode Seats

Closed 410mm	BTC066500	
Open 460mm	BTC066600	
Closed 460mm	BTC066700	
Open 530mm	BTC066750	
Open 600mm	BTC066800	

Aspire Hand Made Pressure Reducing Shower Commode Seats

320mm - Open Front	BTC089122	
320mm - Closed Front	BTC089124	
400mm - Open Front	BTC089126	
400mm - Closed Front	BTC089128	
460mm - Open Front	BTC089130	
460mm - Closed Front	BTC089140	
460mm - Open Left	BTC089150	
460mm - Open Right	BTC089160	
500mm - Open Front	BTC089170	
500mm - Closed Front	BTC089180	
550mm - Open Front	BTC089190	
550mm - Closed Front	BTC089200	
600mm - Open Front	BTC089210	
600mm - Closed Front	BTC089220	
650mm - Open Front	BTC089230	
650mm - Closed Front	BTC089240	

4HC Shower Commode Seats

4HC - Open Front w/Pan Carrier Runners	BTC069510	
4HC - Closed Front w/ Pan Carrier Runners	BTC069520	





Shower Seating

Description	Code	Image
-------------	------	-------

Shower Chairs

Aspire Shower Chair w/Arms - 470mm - Treated Steel - 200kg	BTS118000	
Aspire Shower Chair w/Arms - 470mm - Aluminium - 200kg	BTS118005	
Aspire Shower Chair w/Arms - Wide - 525mm - Treated Steel - 200kg	BTS118010	
Aspire Shower Chair w/Arms - Wide - 525mm - Aluminium - 200kg	BTS118015	
Shower Chair - MYCO Swivel - 445mm Wide - 100kg Weight	BTS107100	

Shower Stools

Aspire Shower Stool w/Arms - 495mm - Treated Steel - 175kg	BTS119000	
Aspire Shower Stool w/Arms - 495mm - Aluminium - 175kg	BTS119005	
Aspire Shower Stool w/Arms - Wide - 525mm - Treated Steel - 175kg	BTS119010	
Aspire Shower Stool w/Arms - Wide - 525mm - Aluminium - 175kg	BTS119015	
Aspire MAXI Shower Stool - Adjustable - Padded Arms & Seat - 575 to 775mm - 310kg	BTS119030	

Bath Seating



Description	Code	Image
-------------	------	-------

Bath Chairs, Benches & Boards

Bath Chair - MYCO Swivel Bather - 710mm - 100kg	BTS106550	
Bath Chair - Breezy Every Day - Swivel Bather - 710mm - 100kg	BTS106500	
Bath Transfer Bench - w/ Arm & Plastic Seat & Backrest - 136kg	BTS108200	
Bath Transfer Bench - Bariatric - Arm Plastic Seat & Backrest - 227kg	BTS105300	
Bath/Shower Board - Plastic w/ Handle & Adj Width	BTS113700	

Shower Trolleys



Description	Code	Image
-------------	------	-------

Shower Trolley - Electric	BTS147100	
Shower Trolley - Aspire Hydraulic - 2150x840x500- 775mm - 150kg	BTS148100	



Bedroom

Over Bed Tables

Description	Code	Image
Over bed Table - Greiner - BT	CHT100050	
Over bed Table - Greiner - BT w/ Split top	CHT100060	

Bed Cradles

Aspire Bed Cradle - White (Fixed)	BEA014605	
Aspire Bed Cradle - White (Adjustable)	BEA014610	

Bedside Commode

Description	Code	Image
Aspire Classic Bedside Commode - Slate - 450mm - 125kg	BEC045006	
Aspire Deluxe Bedside Commode - Champagne - 460mm - 160kg	BEC045115	
Aspire Deluxe Bedside Commode - Slate - 460mm - 160kg	BEC045116	
Aspire MAXI Bedside Commode	BEC045120	



Bedside Cabinet

Description	Code	Image
Aspire Bedside Cabinet - 1 Drw 1 Dr - Compact - 735 x 530 x 505mm	BEA827090	
Aspire Bedside Cabinet - 1 Drw 1 Dr - Laminate - 650 x 455 x 430mm	BEA827100	
Aspire Bedside Cabinet - 2 Drw 1 Shlf - Compact - 745 x 500 x 530mm	BEA827110	
Aspire Bedside Cabinet - 1 Drw 1 Dr - Compact - 755 x 500 x 530mm	BEA827120	
Aspire Bedside Cabinet - 2 Drw - Laminate - 450 x 450 x 450mm	BEA827130	
Aspire Bedside Cabinet - 3 Drw - Laminate - 580 x 500 x 400mm	BEA827140	
Aspire Bedside Cabinet - 3 Drw - Laminate - 615 x 600 x 445mm	BEA827150	
Bedside Cabinet - 4 Drawer (select colour)	BEA828100	
Bedside Cabinet - 2 Drawer + 1 Dump Drawer (select colour)	BEA828110	

Bedside Cabinet


Description	Code	Image
Bedside Cabinet - 1 Drawer + 1 Door (select colour)	BEA828120	
Bedside Cabinet - 2 Drawer + 1 Door (select colour)	BEA828130	
Bedside Cabinet - 4 Drawer + Hutch (select colour)	BEA828150	
Bedside Cabinet - 2 Drawer + 1 Dump Drawer + Hutch (select colour)	BEA828160	
Bedside Cabinet - 1 Drawer + 1 Door + Hutch (select colour)	BEA828170	
Bedside Cabinet - 2 Drawer + 1 Door + Hutch (select colour)	BEA828180	
Bedside Cabinet - 2 Drawer + Open Top (select colour)	BEA828190	
Bedside Cabinet - Drawer Lock (installed)	BEA828200	



Recline Chairs

Aspire Signature Lift Recline Chair - Space Saver

Code	Description	Overall Height	Overall Width	Overall Depth	Seat Width
CHP197700	Space Saver - Small - Mink	1010 mm	780 mm	690 mm	450 mm
CHP197705	Space Saver - Small - Lagoon	1010 mm	780 mm	690 mm	450 mm
CHP197710	Space Saver - Medium - Mink	1050 mm	780 mm	715 mm	480 mm
CHP197715	Space Saver - Medium - Lagoon	1050 mm	780 mm	715 mm	480 mm
CHP197716	Space Saver - Medium - Heritage Vinyl	1050 mm	780 mm	715 mm	480 mm
CHP197720	Space Saver - Large - Mink	1110 mm	780 mm	740 mm	500 mm
CHP197725	Space Saver - Large - Lagoon	1110 mm	780 mm	740 mm	500 mm
CHP197730	Space Saver - Large - Heritage Vinyl	1110 mm	780 mm	740 mm	500 mm












Aspire Signature Lift Recline Chair - Dual Action - Independent Leg Raise & Back

Code	Description	Overall Height	Overall Width	Overall Depth	Seat Width
CHP197735	Dual Action - Small - Mink	1010 mm	780 mm	710 mm	450 mm
CHP197740	Dual Action - Small - Lagoon	1010 mm	780 mm	710 mm	450 mm
CHP197745	Dual Action - Medium - Mink	1050 mm	780 mm	735 mm	480 mm
CHP197750	Dual Action - Medium - Lagoon	1050 mm	780 mm	735 mm	480 mm
CHP197751	Dual Action - Medium - Heritage Vinyl	1050 mm	780 mm	735 mm	480 mm
CHP197755	Dual Action - Large - Mink	1110 mm	780 mm	760 mm	500 mm
CHP197760	Dual Action - Large - Lagoon	1110 mm	780 mm	760 mm	500 mm





Powerlift Recline Chairs



Description	Code	Image
Aspire Verona Lift Recline Chair - Mushroom - Single Motor - 130kg	CHP227100	
Aspire Maui Lift Recline Chair - Mocha - Dual Motor - 130kg	CHP227110	
Aspire Porto Lift Recline Chair - Petite Recliner - Fawn - Single Motor - 150kg	CHP227200	
Aspire Raphael Quattro Lift Recline Chair - Bronze - 4 Motor - 130kg	CHP227300	
Aspire Montana Bariatric Lift Recline Chair - Bronze - Single Motor - 220kg	CHP227400	
Aspire Da Vinci Quattro Lift Recline Chair - Late - 4 Motor - 136kg	CHP227500	
Aspire Da Vinci Quattro Lift Recline Chair - Gunmetal - 4 Motor - 136kg	CHP227510	
Aspire Da Vinci Quattro Lift Recline Chair - Fog - 4 Motor - 136kg	CHP227520	
Aspire Da Vinci Quattro Lift Recline Chair - Dove - 4 Motor - 136kg	CHP227530	

Powerlift Recline Chairs

Description	Code	Image
Ascent Power Mobile Chair	CHP197000	
Synergy Mobile Recliner Chair	CHP197010	

Mobile Recliner Chairs

Watercomfort Power Recline Chairs

Powerlift Recline Chair - Watercomfort - 1 Motor - 500mm Wide - Fabric - 140kg	CHP197270	
Powerlift Recline Chair - Watercomfort - 1 Motor 550mm Wide - Fabric - 140kg	CHP197290	
Powerlift Recline Chair - Watercomfort - 1 Motor - 600mm Wide - Fabric - 140kg	CHP197272	
Powerlift Recline Chair - Watercomfort - 2 Motor - 500mm Wide - Fabric - 140kg	CHP197271	
Powerlift Recline Chair - Watercomfort - 2 Motor - 550mm Wide - Fabric - 140kg	CHP197291	
Powerlift Recline Chair - Watercomfort - 2 Motor - 600mm Wide - Fabric - 140kg	CHP197273	



Therapeutic Recline Chairs

Description	Code	Image
Aspire Pressure Relief Chairs		
Aspire AIR LIFT Chair - Space Saver - Petite - 140kg	CHP198865	
Aspire AIR LIFT Chair - Space Saver - Large - 140kg	CHP198870	
Aspire AIR LIFT Chair - Dual Action - Petite - 140kg	CHP198875	
Aspire AIR LIFT Chair - Dual Action - Large - 140kg	CHP198880	
Aspire MOBILE AIR Chair - Small - 180kg	CHP198850	
Aspire MOBILE AIR Chair - Large - 180kg	CHP198855	
Aspire SHELL Chair - Large - 510mm - 135kg	CHP198915	
Shoalhaven Manual Recliner Chair	CHP198950	

Aspire Mobile Air Chair Accessories

Chair Padded Footrest - Aspire MOBILE AIR Chair	CHP198860	
Fixed Chair Tray - Aspire MOBILE AIR Chair	CHP198861	
Rotational Chair Tray - Aspire MOBILE AIR Chair	CHP198862	
Chair Footplate - Mobile Pressure Recline Chair	CHP198955	
Chair Tray - Mobile Pressure Recline Chair	CHP198957	

Therapeutic Recline Chairs

Description	Code	Image
Seating Matters Pressure Relief Chairs		
Phoenix Chair - Pressure Relief Chair - Large - Manual - 160kg	CHP197805	
Phoenix Chair - Pressure Relief Chair - Large - Electric Leg & Tilt - 160kg	CHP197810	
Phoenix Chair - Pressure Relief Chair - Large - Electric Leg, Recline & Tilt - 160kg	CHP197815	
Sorrento Chair - Pressure Relief Chair - Large - Manual - 160kg	CHP197822	
Sorrento Bariatric Chair - Pressure Relief Chair - Electric - 294kg	CHP197823	

Seating Matters Chairs Accessories


Tray Table - All Seating Matters Chairs	CHP197875	
4 Point Seat Belt - All Seating Matters Chairs	CHP197880	
Seat Cushion - 350mm - Phoenix Paed Chair	CHP197910	
Seat Cushion - 450mm - All Seating Matters Chairs	CHP197915	
Seat Cushion - 500mm - All Seating Matters Chairs	CHP197920	
Seat Cushion - Custom - All (include dimensions)	CHP197925	

Watercomfort Pressure Relief Chairs



Watercomfort - 1 Motor - Custom/Pressure Care - 140kg	CHP197274	
Watercomfort - 2 Motor - Custom/Pressure Care - 140kg	CHP197275	
Watercomfort - 1 Motor Wide - Custom/Pressure Care - 140kg	CHP197276	
Watercomfort - 2 Motor Wide - Custom/Pressure Care - 140kg	CHP197277	



Therapeutic Recline Chairs


Description	Code	Image
Watercomfort Ambassador HD - 1 Motor - Pressure Care - 140kg	CHP197278	
Watercomfort Ambassador HD - 2 Motor - Pressure Care - 140kg	CHP197279	
Watercomfort Ambassador HD - 2 Motor 600 mm Wide - Pressure Care - 160kg	CHP197280	

Therapeutic Recline Chairs

Description	Code	Image
Watercomfort - 1 Motor - 550mm Wide - Pressure Care - 140kg	CHP197292	
Watercomfort - 2 Motor - 600mm Wide - Pressure Care - 160kg	CHP197293	
Watercomfort - 1 Motor - 500,550 or 600mm Wide - Custom Frame / Pressure Care - 140kg	CHP197305	
Watercomfort - 2 Motor - 500,550 or 600mm Wide - Custom Frame / Pressure Care - 140kg	CHP197310	



Product brochures also available! Please contact us for a copy




Day Chairs



Aspire Height Adjustable Back Day Chairs

Code	Description	Overall Height	Overall Width	Overall Depth	Backrest Height
CHP208025	Aspire Adjustable Day Chair - Latte Vinyl	1070 - 1220 mm	575 - 675 mm	760 - 860 mm	740 - 790 mm
CHP208030	Aspire Adjustable Day Chair - Ink Vinyl	1070 - 1220 mm	575 - 675 mm	760 - 860 mm	740 - 790 mm



Day Chairs

Description	Code	Image
-------------	------	-------

Aspire Waterfall Highback Chairs

Chair Highback - Aspire Waterfall Day Chair - Oatmeal Fab - 535mm - 200kg	CHP208075	
--	-----------	--

Aspire Classic Lowback Chair

Classic Lowback Day Chair - Champ Vinyl - 460mm - 160kg	CHP208000	
Classic Lowback Day Chair - Slate Vinyl - 460mm - 160kg	CHP208005	

Aspire Classic Highback Day Chair

Classic Highback Day Chair - Champ Vinyl - 490mm - 160kg	CHP208050	
Classic Highback Day Chair - Slate - 490mm - 160kg	CHP208055	

Day Chairs

Description	Code	Image
-------------	------	-------

Aspire MAXI Day Chair

Aspire MAXI Day Chair - Vinyl	CHP208010	
----------------------------------	-----------	--

Accessories

Chair Footrest - Adjustable - Padded - Aspire - Champagne Vinyl	CHP208080	
Chair Footrest - Adjustable - Padded - Aspire - Slate Vinyl	CHP208085	


General Ward Equipment



General Ward Equipment

Description	Code	Image
-------------	------	-------



Mobile IV Stand

IV pole - Mobile - 75 mm Grey Rubber Castors	WAT820120	
IV pole - Mobile - 100 mm Grey Rubber Castors	WAT820130	
IV pole - Mobile - 100 mm Grey Castors + Push Ring + 4 Hooks	WAT820140	

General Ward Equipment

Description	Code	Image
-------------	------	-------

Aspire IV Poles

IV Pole - Aspire - 5 Star Polyurethane Base w/ bottle holder	WAT820180	
IV Pole - Stackable - Aspire - Single-Handed Height Adjustment	WAT820185	






For more information, please visit our [Hospital Equipment Range Catalogue](#)

Instrument/ Dressing Trolleys








Instrument Trolleys

Description	Code	Image
IV Instrument Trolley 500x500 Square frame	WAT900800	
Instrument Trolley 500x500 Square frame + drawer	WAT900810	
Instrument Trolley 500x500 Square frame + 2 drawers	WAT900820	

Instrument Trolley - Flat Top

Instrument Trolley - Flat top 500x500x950	WAT900880	
Instrument Trolley - Flat top 500x800x950	WAT900890	
Instrument Trolley - Flat top 500x1000x950	WAT900900	

Dressing Trolleys

Description	Code	Image
Dressing Trolley 500x800 Square frame	WAT900840	
Dressing Trolley 500x800 Square frame + 1 drawer	WAT900850	
Dressing Trolley 500x800 Square frame + 2 drawers (Full length)	WAT900860	
Dressing Trolley 500x800 Square frame + 2 drawers (side by side)	WAT900861	
Dressing Trolley 500x800 Square frame + 4 drawers	WAT900870	

Pressure Care Cushions



Pressure Care Cushions

Description	Code	Image
-------------	------	-------

JAY J2 Cushions

14 x 16in	PTC563400	
16 x 18in	PTC562700	
16 x 16in	PTC562500	
16 x 20in	PTC563000	
17 x 17in	PTC563800	
18 x 16in	PTC561100	
18 x 18in	PTC561300	
18 x 20in	PTC562100	
20 x 16in	PTC563700	
20 x 18in	PTC564100	
20 x 20in	PTC561900	
24 x 20in	PTC562400	

JAY J2 Deep Contour Cushions

14 x 14in	PTC565300	
14 x 16in	PTC565400	
15 x 15in	PTC565700	
15 x 17in	PTC565800	
16 x 16in	PTC566000	
16 x 18in	PTC566100	
16 x 20in	PTC565900	
17 x 15in	PTC566300	
17 x 17in	PTC566400	
18 x 16in	PTC566600	
18 x 18in	PTC566700	
18 x 20in	PTC566500	
20 x 16in	PTC565150	
20 x 18in	PTC565000	
20 x 20in	PTC564900	
22 x 18in	PTC565200	

Pressure Care Cushions

Description	Code	Image
-------------	------	-------

JAY Basic Cushions

14 x 16in	PTC567600	
15 x 16in	PTC568400	
16 x 16in	PTC567400	
16 x 18in	PTC567500	
17 x 16in	PTC568450	
18 x 16in	PTC566800	
18 x 18in	PTC566900	
20 x 16in	PTC567650	
20 x 18in	PTC567700	
22 x 18in	PTC567750	
22 x 20in	PTC566950	

JAY J2 Plus Bariatric Cushions

20 x 18in	PTC567000	
20 x 20in	PTC567002	
21 x 19in	PTC567050	
21 x 20in	PTC567075	
22 x 18in	PTC567100	
22 x 19in	PTC567150	
22 x 20in	PTC567200	
22 x 22in	PTC567004	
22 x 22in	PTC567250	
24 x 18in	PTC567300	

JAY GS Cushions

10 x 13in	PTC558800	
12 x 15in	PTC559000	
14 x 17in	PTC558700	
16 x 19in	PTC558500	
18 x 20in	PTC558300	



Pressure Care Cushions

Description	Code	Image
14 x 14in	PTC573468	
14 x 16in	PTC573469	
15 x 16in	PTC573459	
16 x 16in	PTC573460	
16 x 18in	PTC573463	
17 x 16in	PTC573475	
17 x 17in	PTC573467	
18 x 16in	PTC573461	
18 x 17in	PTC573474	
18 x 18in	PTC573462	
20 x 16in	PTC573464	
20 x 17in	PTC573470	
20 x 18in	PTC573465	
20 x 20in	PTC573466	
22 x 20in	PTC573473	

JAY Union Cushions

14 x 14in	PTC573420	
16 x 17in	PTC573433	
16 x 16in	PTC573423	
16 x 18in	PTC573429	
17 x 17in	PTC573419	
17 x 18in	PTC573425	
18 x 16in	PTC573422	
18 x 18in	PTC573426	
19 x 17in	PTC573421	
20 x 17in	PTC573424	
20 x 18in	PTC573418	
22 x 24in	PTC573427	

JAY Fusion Cushions

14 x 16in	PTC571207	
16 x 17in	PTC571251	
16 x 16in	PTC571204	
16 x 18in	PTC571206	
17 x 16in	PTC571215	
17 x 17in	PTC571205	
17 x 18in	PTC571214	
17 x 20in	PTC571246	
18 x 20in	PTC571247	
18 x 21in	PTC571252	
19 x 19in	PTC571216	
19 x 17in	PTC571250	
19 x 20in	PTC571249	
20 x 18in	PTC571230	
20 x 19in	PTC571231	
22 x 18in	PTC571240	
22 x 22in	PTC571245	

Pressure Care Cushions

Description	Code	Image
14 x 14in Flat Bottom	PTC580002	
14 x 16in Flat Bottom	PTC580005	
15 x 15in Flat Bottom	PTC580100	
16 x 16in Flat Bottom	PTC580300	
17 x 17in Flat Bottom	PTC580350	
20 x 20in Flat Bottom	PTC580660	
14 x 16in Curved Bottom	PTC580004	
15 x 15in Curved Bottom	PTC580050	
16 x 16in Curved Bottom	PTC580200	
16 x 18in Curved Bottom	PTC580400	
18 x 16in Curved Bottom	PTC580500	
18 x 18in Curved Bottom	PTC580600	
19 x 16in Curved Bottom	PTC580640	
20 x 20in Curved Bottom	PTC580650	

JAY X2 Cushions

16 x 16in	PTC561270	
16 x 18in	PTC561271	
17 x 17in	PTC561274	
18 x 16in	PTC561273	
18 x 18in	PTC561272	

Equagel General Cushions


16in x 16in	PTC551043	
16in x 18in	PTC551045	
16in x 20in	PTC551047	
18in x 16in	PTC551049	
18in x 18in	PTC551051	
18in x 20in	PTC551053	
20in x 16in	PTC551055	
20in x 18in	PTC551057	
20in x 20in	PTC551059	
22in x 16in	PTC551061	
22in x 18in	PTC551063	
22in x 20in	PTC551065	

Equagel Adjustable Cushions

16in x 16in	PTC551093	
16in x 18in	PTC551095	
18in x 16in	PTC551096	
18in x 18in	PTC551097	
20in x 16in	PTC551099	
20in x 18in	PTC551101	
22in x 16in	PTC551103	
22in x 18in	PTC551105	
24in x 18in	PTC551109	




Pressure Care Cushions

Description	Code	Image
16 x 16in	PTC547200	
18 x 16in	PTC547100	
18 x 18in	PTC547000	
20 x 20in	PTC546990	
Cushion - Cover for Action Gel (*Specify Size*)	PTC547210	

Action Gel Pad Cushion

Pressure Care Cushions

Description	Code	Image
440 x 420mm	GSS340100	
490 x 460mm	GSS340104	

Diffuser Cushions

Cushions Covers

Description	Code
-------------	------

JAY Cushion Covers

15 x 17 in - Lite	PTC571984
16 x 16 in - Lite	PTC571980
17 x 18 in - Lite	PTC571988
18 x 20 in - Lite	PTC571992
15.5 x 18 in - Stretch	PTC576800
17 x 17 in - Stretch	PTC577500
18 x 18 in - Stretch	PTC575700
20 x 18 in - Stretch	PTC577800

JAY Cushion Covers - Incontinence

14 x 16 in	PTC577300
15.5 x 16 in	PTC576700
15.5 x 18 in	PTC577000
15.5 x 20 in	PTC577100
16 x 16 in	PTC574800
16 x 18 in	PTC578600
17 x 17 in	PTC577700
18 x 16 in	PTC573500
18 x 16 in	PTC575600
18 x 18 in	PTC573700
18 x 18 in	PTC575900
18 x 20 in	PTC576400
20 x 18 in	PTC577825
20 x 20 in	PTC576100
14 x 17in - GS	PTC574100
16 x 19in - GS	PTC574000
18 x 20in - GS	PTC573900
18 x 16 in - Active Incontinence	PTC574500
20 x 18 in - Active Incontinence	PTC574600

Cushions Covers

Description	Code
-------------	------

JAY Cushion Covers - Air Exch

12 x 15 in	PTC574250
14 x 16 in	PTC575100
15.5 x 16 in	PTC576600
15.5 x 18 in	PTC576900
16 x 19 in	PTC573950
16 x 16 in	PTC574700
16 x 18 in	PTC575000
17 x 17 in	PTC577600
18 x 16 in	PTC575500
18 x 18 in	PTC573600
18 x 18 in	PTC575800
18 x 20 in	PTC576300
18 x 16 in - Active Air Exch	PTC574400
18 x 18 in - Active Air Exch	PTC574550

JAY Cushion Covers - Deep Contour


16 x 16 in	PTC578200
16 x 18 in	PTC578400
18 x 18 in	PTC579000
18 x 20 in	PTC578800
20 x 18 in	PTC577980
16 x 18 in - Air Exch	PTC578500
16 x 20 in - Air Exch	PTC578000
18 x 18 in - Air Exch	PTC579100
16 x 16 in - Incontinence	PTC578300
16 x 20 in - Incontinence	PTC578100
17 x 17 in - Incontinence	PTC578700
18 x 18 in - Incontinence	PTC579200
18 x 20 in - Incontinence	PTC578900
20 x 20 in - Incontinence	PTC577975

Aspire Patient Lifters & Slings





Aidacare A150F Folding Aluminium Patient Lifter

Code	Description	Overall Height	Overall Length	Overall Width	Lifter Weight
LSS390600	Lifter A150F - Folding Lifter - Aluminium	1873 mm	1280 mm	660 mm	32.9 kg




Aidacare A205 Aluminium Compact Lifter

Code	Description	Overall Height	Overall Length	Overall Width	Lifter Weight
LSS390610	Lifter A205 - Patient Lifter - Aluminium	2045 mm	1135 mm	620 mm	38.1 kg
GSP390938	Push Handle Padding - Aidacare Aspire 200/200S/A200S/A205				



Aidacare 200 Steel Patient Lifter


Code	Description	Overall Height	Overall Length	Overall Width	Lifter Weight
LSS390620	Lifter 200 - Patient Lifter - Steel	1940 mm	1280 mm	665 mm	43.9 kg
GSP390938	Push Handle Padding - Aidacare Aspire 200/200S/A200S/A205				





Aidacare A200S Aluminium Standing Lifter

Code	Description	Overall Height	Overall Length	Overall Width	Lifter Weight
LSS390640	Lifter A200S - Stander - Aluminium	1455 mm	985 mm	590 mm	30.4 kg
GSP390910	Sling Bar - Aidacare Aspire A200S				
GSP390910H	Sling Bar with Grip Handles - Aidacare Aspire A200S				
GSP390938	Push Handle Padding - Aidacare Aspire 200/200S/A200S/A205				



Aidacare 200S Steel Standing Lifter

Code	Description	Overall Height	Overall Length	Overall Width	Lifter Weight
LSS390650	Lifter 200S - Patient Stander - Steel	1790 mm	1150 mm	655 mm	44.9 kg
GSP390938	Push Handle Padding - Aidacare Aspire 200/200S/A200S/A205				



Aidacare A320 Aluminium Patient Lifter

Code	Description	Overall Height	Overall Length	Overall Width	Lifter Weight
LSS390630	Lifter A320 - Bariatric Lifter - Aluminium	2165 mm	1505 mm	765 mm	63 kg



aspireswift Patient Mover

Code	Description	Overall Height	Overall Length	Overall Width	Knee Pad Height	Seat Pad Height
LSS390590	Standing & Transport Aid - Adjustable Legs	1060 mm	820 mm	490 - 670 mm	250 - 490 mm	620 - 670 mm



Aspire Pivot Frame

Description	Code	Image
-------------	------	-------


Aspire Pivot Frame

Pivot Frame - Electric - 227kg	LSS390665	
Pivot Frame - Manual - 227kg	LSS390670	

Aidacare Aspire Inline Weigh Scale

Description	Code	Image
-------------	------	-------

Aidacare Aspire Inline Weigh Scale

Inline Weigh Scale - 320kg	LSS390680	
----------------------------	-----------	---




Aspire Patient Slings

Description	Code	Image
-------------	------	-------


Aspire Deluxe General Purpose Sling

Polyester - Small - 200kg	LSS390700	
Polyester - Medium - 200kg	LSS390705	
Polyester - Large - 300kg	LSS390710	
Polyester - XLarge - 300kg	LSS390715	
Mesh - Small - 200kg	LSS390716	
Mesh - Medium - 200kg	LSS390717	
Mesh - Large - 300kg	LSS390718	
Mesh - XLarge - 300kg	LSS390719	


Aspire Deluxe General Purpose Sling w/ Head Support

Polyester - Small - 200kg	LSS390740	
Polyester - Medium - 200kg	LSS390745	
Polyester - Large - 300kg	LSS390750	
Polyester - XLarge - 300kg	LSS390755	
Polyester - XXLarge - 300kg	LSS390751	
Polyester - XXXLarge - 300kg	LSS390752	
Mesh - Small - 200kg	LSS390756	
Mesh - Medium - 200kg	LSS390757	
Mesh - Large - 300kg	LSS390758	
Mesh - XLarge - 300kg	LSS390759	
Mesh - XXLarge - 300kg	LSS3907591	
Mesh - XXXLarge - 300kg	LSS3907592	

Aspire Deluxe General Purpose Sling w/ Head Support & Clips

Polyester - Small - 200kg	LSS390900	
Polyester - Medium - 200kg	LSS390905	
Polyester - Large - 300kg	LSS390910	
Polyester - XLarge - 300kg	LSS390915	
Mesh - Small - 200kg	LSS390916	
Mesh - Medium - 200kg	LSS390917	
Mesh - Large - 300kg	LSS390918	
Mesh - XLarge - 300kg	LSS390919	

Aspire Deluxe Hygiene/Access Sling - Padded Polyester

Small - 200kg	LSS390760	
Medium - 200kg	LSS390765	
Large - 300kg	LSS390770	
XLarge - 300kg	LSS390775	
XXLarge - 300kg	LSS390776	
XXXLarge - 300kg	LSS390777	

Aspire Deluxe Hygiene/Access Sling w/Head Support - Padded Polyester

Small - 200kg	LSS390780	
Medium - 200kg	LSS390785	
Large - 300kg	LSS390790	
XLarge - 300kg	LSS390795	

Aspire Patient Slings

Description	Code	Image
-------------	------	-------

Aspire Deluxe Hygiene/Access Sling w/Head Support & Clips

Polyester - Small - 200kg	LSS390940	
Polyester - Medium - 200kg	LSS390945	
Polyester - Large - 300kg	LSS390950	
Polyester - XLarge - 300kg	LSS390955	


Aspire Deluxe Hammock w/Head Support

Mesh - Small - 200kg	LSS390860	
Mesh - Medium - 200kg	LSS390865	
Mesh - Large - 300kg	LSS390870	
Mesh - XLarge - 300kg	LSS390875	

Aspire All Day General Purpose w/Head Support Parasilk

Small - 200kg	LSS390880	
Medium - 200kg	LSS390885	
Large - 300kg	LSS390890	
XLarge - 300kg	LSS390895	
Clips - Small - 200kg	LSS390960	
Clips - Medium - 200kg	LSS390965	
Clips - Large - 300kg	LSS390970	
Clips - XLarge - 300kg	LSS390975	

Aspire Deluxe Padded Standing Sling - Polyester

Small - 200kg	LSS390720	
Medium - 200kg	LSS390725	
Large - 300kg	LSS390730	
XLarge - 300kg	LSS390735	
XXLarge - 300kg	LSS390736	
XXXLarge - 300kg	LSS390737	


Aspire Deluxe Padded Standing & Clips - Polyester

Small - 200kg	LSS390920	
Medium - 200kg	LSS390925	
Large - 300kg	LSS390930	
XLarge - 300kg	LSS390935	



Product brochures also available!

Please contact us for a copy




Liko Patient Lifters & Slings




Liko Patient Lifters

Description	Code	Image
-------------	------	-------


Golvo 9000 Patient Lifter

Golvo 9000 - 200kg SWL - Universal Slingbar 450 included	LSS393100	
--	-----------	---


Viking M Patient Lifter

Viking M - 205kg SWL - Universal Slingbar 450 included	LSS393190	
--	-----------	---

Viking L Patient Lifter

Viking L - 250kg SWL - Universal Slingbar 450 included	LSS393180	
--	-----------	---

Viking XL Patient Lifter

Viking XL - 300kg SWL - Universal TwinBar 670	LSS393170	
---	-----------	---


Liko Patient Lifters

Description	Code	Image
-------------	------	-------


Sabina II EE

Sabina II EE - 2-Speed Lift - Electric Legs - 200kg SWL (Sling bar separate)	LSS393250	
Sabina II Side Support - Includes screw and nut	LSS393290	
Sabina II 350 SlingBar	LSS393270	
Sabina II Comfort SlingBar - 600 mm (23.6 in)	LSS393280	

RollOn - Max 160kg

RollOn - Max 160 kg	LSS393360	
---------------------	-----------	---

Spreader Bar - Universal Sling Bar


Universal SlingBar 450 with Quick-release Hook - 300 kg	LSS393520	
---	-----------	---




Liko Slings

Description	Code	Image
-------------	------	-------

Liko Original Highback Sling

Polyester - XS - 200kg	LSS394610	
Polyester - S - 200kg	LSS394620	
Polyester - M - 200kg	LSS394630	
Polyester - M-Slim - 200kg	LSS394685	
Polyester - L - 200kg	LSS394640	
Polyester - XL - 500kg	LSS394650	
Mesh - XS -200kg	LSS394660	
Mesh - S - 200kg	LSS394670	
Mesh - M - 200kg	LSS394680	
Mesh - L - 200kg	LSS394690	
Mesh - XL - 500kg	LSS394700	
Net (Bath) - S - 200kg	LSS394705	
Net (Bath) - M-Slim - 200kg	LSS394676	
Net Polyester - M-Slim - 200kg	LSS394675	
Net Polyester - M - 200kg	LSS367854	
Net Polyester - XL - 200kg	LSS367856	

Liko Soft Original Highback Sling

Polyester - M-Slim - 200kg	LSS394560	
Polyester - M - 200kg	LSS394570	
Polyester - L - 200kg	LSS394580	
Polyester - XL - 500kg	LSS394590	
Polyester - XXL 500kg	LSS394600	

Liko Solo Highback Sling

M (Slim) - 200kg	LSS394740	
M - 200kg	LSS394750	
L - 200kg	LSS394760	
No Wash -XL - 500kg	LSS394770	

Liko UltraSling Bariatric Sling

Polyester - SHORT - 500kg	LSS394400	
Polyester - REGULAR - 500kg	LSS394410	
Polyester - LONG - 500kg	LSS394420	
Mesh - REGULAR - 500kg	LSS394430	

Liko SilhouetteSling

Mesh - XS - 200kg	LSS394450	
Mesh - Sml - 200kg	LSS394460	
Mesh - Med - 200kg	LSS394470	
Mesh - L - 200kg	LSS394440	

Liko UniversalSling

Polyester - M - 200kg	LSS394775	
Polyester - L - 200kg	LSS394774	
Polyester - XL - 300kg	LSS394773	

Liko TeddySling Soft Original - Paediatric

Polyester - XS - 50kg	LSS394100	
Polyester - S - 50kg	LSS394110	


Liko Slings

Description	Code	Image
-------------	------	-------

Liko ComfortSling

Mesh - M - 200kg	LSS394710	
Mesh - L - 200kg	LSS394720	
Mesh - XL - 300kg	LSS394730	
Plus 300 - Net - M - 200kg	LSS394737	
Plus 300 - Mesh - XL - 300kg	LSS394736	
Plus 360 - Mesh - L - 200kg	LSS394733	
Plus 360 - Mesh - M - 200kg	LSS394732	
Plus 360 - Mesh - XL - 500kg	LSS394734	
Plus High - Net Polyester, Padded Seat - M - 200kg	LSS394735	
Plus High - Hygiene Opening - Net Polyester - L - 200kg	LSS394731	
Plus High - Hygiene Opening - Net (Bath) - M - 200kg	LSS394738	

Liko HygieneSling

Polyester - S - 200kg	LSS394473	
Polyester - M - 200kg	LSS394474	
Polyester - L - 200kg	LSS394475	
Belt - Polyester - S - 200kg	LSS394480	
Belt - Polyester - M - 200kg	LSS394490	
Belt - Polyester - L - 200kg	LSS394500	
Belt - Polyester - XL - 300kg	LSS394510	


Liko AmputeeSling

Net (bathing) - S - 200kg	LSS394514	
Net (bathing) - M - 200kg	LSS394516	
Net (bathing) - L - 200kg	LSS394518	
Highback - S - 200kg	LSS394520	
Highback - M - 200kg	LSS394530	
Highback - L - 200kg	LSS394540	
Highback - XL - 300kg	LSS394550	

Liko SupportVest Sling - Fits Sabina II 350 SlingBar

S - w/2 Loop Clips - 200kg	LSS394120	
M - w/2 Loop Clips - 200kg	LSS394130	
L - w/2 Loop Clips - 200kg	LSS394140	
XL - w/2 Loop Clips - 200kg	LSS394150	

Liko SafetyVest Sling - Fits Sabina II 350 SlingBar

M - w/4 Loop Clips - 200kg	LSS394160	
L - w/4 Loop Clips - 200kg	LSS394170	

Liko ComfortVest Sling - Fits Sabina II 350 SlingBar

S - w/4 Loop Clips - 200kg	LSS394180	
M - w/4 Loop Clips - 200kg	LSS394190	
L - w/4 Loop Clips - 200kg	LSS394200	
XL - w/4 Loop Clips - 200kg	LSS394210	


Ceiling Hoists



Prism Ceiling Hoists

Description	Code	Image
-------------	------	-------


Prism CP200 w/ Quick Release System

Prism CP200 w/ Quick Release System - 200kg	LIC350105	
---	-----------	---

Prism P200 Portable

Prism P200 Portable - Manual Traverse w/ Quick Release System - 200kg	LIC350110	
Prism P200 Portable - Manual Traverse w/ Quick Release System, Trolley & Reacher Bar - 200kg	LIC350110K	
Prism P200 Portable - Manual Traverse w/ Reacher Bar - 200kg	LIC350110KR	

Prism Transactive XTRA Ceiling Hoist

Prism Transactive XTRA Fixed - Manual Traverse - 270kg	LIC350200	
Prism Transactive XTRA Fixed - Powered Traverse - 270kg	LIC350210	


Prism Ceiling Hoists

Description	Code	Image
-------------	------	-------

C380 Bariatric Fixed Ceiling Hoist

Prism Bariatric C380 Manual Traverse - 380kg	LIC350250	
Prism Bariatric C380 Powered Traverse - 380kg	LIC350260	

Prism Free Standing Gantry

2 Post Free Standing Gantry 200kg	LIC352105	
2 Post Pressure-Fit Gantry System 200kg	LIC352120	

Kit - Ceiling Hoists & Track Components


3m Track - For Permanent Motor - 270kg	LIC353120K
3m Track - For Portable Motor - 270kg	LIC353120KP
6m Track - For Permanent Motor - 270kg	LIC353150K
6m Track - For Portable Motor - 270kg	LIC353150KP



Liko Ceiling Hoists

Description	Code	Image
-------------	------	-------

Multirall 200 Portable Ceiling Hoist

Liko Multirall 200 - 200kg	LIC359100	
Hand Control	LIC359110	
Carriage S50	LIC359120	
Carriage D45 (double hook)	LIC359130	
Carriage S65 - (single hook)	LIC359140	


LikoGuard L/XL Fixed Ceiling Hoist

LikoGuard L - 272kg	LIC359300	
LikoGuard XL - 363kg	LIC359310	

Likorall 200 Fixed Ceiling Hoist

Likorall 200 - natural - 200kg	LIC359490	
--------------------------------	-----------	--

Likorall 250 Fixed Ceiling Hoist

Likorall 250 ES - white - 250kg	LIC359520	
---------------------------------	-----------	---

Liko Ceiling Hoist Accessories

Description	Code	Image
-------------	------	-------

Liko SlingGuard Spreader Bar

450 fixed - 363kg	LIC359320	
670 twin - 363kg	LIC359330	
450 Quick Hook Multi - 363kg	LIC359340	
670 twin with Quick-Hook Multi - 363kg	LIC359350	

Accessories

Hook for SlingBar - Liko Universal SlingBar 350, 450 or 600.	LIC359240
Hand Control - Likorall S, ES, 2-button (for operating lifting motion)	LIC359540



Transfer Boards & Sheets




Transfer Boards

Description	Code	Image
-------------	------	-------

Transfer Board - The Slider

610x230mm No Cut Out	TSE672810	
540x360mm - w/cut out	TSE672800	
645x297mm	TSE672790	
645x360mm	TSE672780	

Transfer Board - Curved

Transfer - Board - Curved Q2	TSE672192	
------------------------------	-----------	---

Transfer Board - Sallyboard

Large - 180x58cm	TSE672196	
Medium - 150x58cm	TSE672195	
Curved	TSE672191	


Transfer Sheets

Description	Code	Image
-------------	------	-------

Aspire Transfer Slide Sheet

Aspire Transfer Sheet - Large - 2000x1450mm	TSE673080	
---	-----------	---

Aspire Slide Sheet

Aspire One Way Slide - Non Slip	TSE673050	
Aspire One Way Slide - Foot Operated - Non Slip	TSE673052	
Aspire Positioning Slide	TSE673054	



Transfer & Walk Aids

Transfer & Walk Aids

Description	Code	Image
-------------	------	-------

Transfer Walk Belt w/ Buckle

630-1140mm - Small	TSE672040	
1010-1570mm - Large	TSE672030	

Air Assisted Lateral Transfer Mat

Disposable Waterproof Flat Sheet (Box of 50)	TSE674480
Single Patient Use - 860 x 1980mm (Box of 10)	TSE674440
Air Supply 1200W	TSE674450
Air Assisted Lateral Transfer Mat - 1.7m Replacement Supply Hose	TSE674460
Transport Stand - Single Basket	TSE674470


Transfer & Walk Aids

Description	Code	Image
-------------	------	-------

Transfer Standing Patient Turner Orbiturn

Transfer - Standing Patient Turner Orbiturn	TSE672935	
---	-----------	---

Aspire Swivel Cushion

Transfer - Swivel Cushion - Aspire	TSE673056	
------------------------------------	-----------	---



Introducing our Aspire Lifter & Sling Product Video



<https://www.aidacare.com.au/knowledge/videos/>

Linen Skips



Linen Skips

Description	Code	Image
-------------	------	-------

Linen Skips - No Lids

Stainless Steel + Grey rubber castors - single	LAC500800	
Stainless Steel + Grey rubber castors - double	LAC500810	
Mild steel Epoxy powder coated + Plastic twin wheel - single	LAC500830	
Mild steel Epoxy powder coated + Plastic twin wheel - double	LAC500840	

Linen Skips

Description	Code	Image
-------------	------	-------

Linen Skip - Foot Operated Lid

Stainless Steel + foot operated lid + Grey rubber castors - single	LAC500860	
Stainless Steel + foot operated lid + Grey rubber castors - double	LAC500870	
Mild steel Epoxy powder coated + foot operated lid + twin wheel - single	LAC500890	
Mild steel Epoxy powder coated + foot operated lid + twin wheel - double	LAC500900	



Linen Skip Accessories

Description	Code	Image
Lid for linen skip - White	LAC500636	
Sticker kit - set of 4 stickers - Yellow, Red, Green Blue	LAC500915	
Bag support (Clip On) - for single soiled linen trolley	LAC500920	
Push handle - for single soiled linen trolley	LAC500925	
Waste Bin - (Clip on) - suits ALL - Includes 30L bin	LAC500926	
Buffer disc	LAC500930	

Linen Bags

Description	Code	Image
Waterproof - Blue	LAC353020	
Waterproof - Black	LAC353030	
Waterproof - Green	LAC353040	
Waterproof - Red	LAC353050	
Waterproof - White	LAC353060	
Waterproof - Yellow	LAC353070	
Half Size (OHS) - White	LAC353105	
Half Size (OHS) - Blue	LAC353106	
Half Size (OHS) - Green	LAC353107	
Half Size (OHS) - Red	LAC353108	
Half Size (OHS) - Yellow	LAC353109	
Half Size (OHS) - Purple	LAC353110	
Full Size - White	LAC353130	
Full Size - Blue	LAC353140	
Full Size - Green	LAC353160	
Full Size - Red	LAC353170	
Drawstring S4 - Yellow	LAC353180	
Drawstring S4 - Purple	LAC353190	



Contact us for a complete range of our
HOSPITAL EQUIPMENT

Ramps



Ramps


Description	Code	Image
-------------	------	-------

Depac EBL Ramps - Edge Barrier Limited Ramps


Ramp - Depac - EBL 1200mm	RAM656090	
Ramp - Depac - EBL 1650mm	RAM656110	
Ramp - Depac - EBL 3500mm	RAM656150	

Ramps

Description	Code	Image
-------------	------	-------

Ramp - Depac - EBL 900mm	RAM656170	
-----------------------------	-----------	---

Depac Ramps - Personal

Ramp - Depac - Personal	RAM656200	
-------------------------	-----------	---

Manual Wheelchairs



Aspire Evoke 2 & 2 HD Wheelchair

Features & Benefits:

- Seat & Backrest Height Adjustable
- Customisable Backrest
- Seat Depth Adjustable
- Height and angle adjustable front castors (8")
- Folding Lightweight Aluminium Design
- Height Adjustable back cranes 17" - 19"
- Optional Contoured Padded Overlay
- Swing-back Armrests
- Swing Away and removable legrests
- Height and angle adjustable footrests
- Quick release 24" solid rear wheels



Code	MWS449500	MWS449510	MWS449520	MWS449530	MWS449540 (HD)	MWS449550 (HD)
Seat Width	350 mm	400 mm	450 mm	500 mm	570 mm	610 mm
Seat Depth	375 - 525 mm	375 - 525 mm	375 - 525 mm	375 - 525 mm	375 - 525 mm	375 - 525 mm
Seat Height	440 - 480 mm	440 - 480 mm	440 - 480 mm	440 - 480 mm	440 - 480 mm	440 - 480 mm
Overall Width	560 mm	610 mm	660 mm	710 mm	780 mm	820 mm
Backrest Height	430 - 490 mm	430 - 490 mm	430 - 490 mm	430 - 490 mm	430 - 490 mm	430 - 490 mm
Armrest Height	205 - 225 mm	205 - 225 mm	205 - 225 mm	205 - 225 mm	205 - 225 mm	205 - 225 mm
SWL	140 kg	140 kg	140 kg	140 kg	180 kg	180 kg



Aspire Lite Transit Wheelchair - Champagne

Code	MWS442301
Seat Width	460 mm
Seat Depth	400 mm
Seat Height	460 mm
Overall Width	600 mm
Backrest Height	465 mm
Armrest Height	235 mm
SWL	120 kg



Features & Benefits:

- Ultra-lightweight wheelchair comes with attendant brakes fitted as standard
- Folding frame for easy storage and transport
- Weighs just 11.5kg
- Ergonomic handles – provides comfort for the caregiver
- Push button, height adjustable arm rests
- Swing away, flip up foot plates – this facilitates user transfers
- 12" rear wheels – with easy to access brakes, for improved riding over outdoor terrain



Aspire Lite Wheelchair - Blue

Code	MWS442300
Seat Width	460 mm
Seat Depth	400 mm
Seat Height	460 mm
Overall Width	550 mm
Backrest Height	465 mm
Armrest Height	235 mm
SWL	120 kg



Features & Benefits:

- An ultra-light, folding frame – for easy storage and transport
- Weighs just 9.5kg
- Ergonomic handles – provides comfort for the caregiver
- Push button, height adjustable arm rests
- Swing away, flip up foot plates – this facilitates user transfers.
- Rear wheel locks – for stability and security.



Aspire Transit 2 Manual Folding Wheelchair

Code	MWS449410	MWS449420	MWS449430
Seat Width	400 mm	450 mm	500 mm
Seat Depth	400 mm	400 mm	400 mm
Seat Height	460 - 500 mm	460 - 500 mm	460 - 500 mm
Overall Width	540 mm	590 mm	640 mm
Backrest Height	440 mm	440 mm	440 mm
Armrest Height	210 mm	210 mm	210 mm
SWL	140 kg	140 kg	140 kg



Features & Benefits:

- Folding Steel Frame
- Padded Nylon Upholstery
- Optional Contoured Padded Overlay
- Quick Release Solid 12" Rear Wheels & Height Adjustable, 8" Castors
- Dacron Fire Retardent Fabric
- Swing-Away, Removable Armrests
- Attendant Push-to-lock Brakes
- Removable Swing Away Legrests & Height Adjustable Footrest



Aspire Assist 2 Manual Folding Wheelchair

Code	MWS449300	MWS449310	MWS449320	MWS449330
Seat Width	350 mm	400 mm	450 mm	500 mm
Seat Depth	400 mm	400 mm	400 mm	400 mm
Seat Height	460 - 500 mm	460 - 500 mm	460 - 500 mm	460 - 500 mm
Overall Width	570 mm	620 mm	670 mm	720 mm
Backrest Height	440 mm	440 mm	440 mm	440 mm
Armrest Height	210 mm	210 mm	210 mm	210 mm
SWL	140 kg	140 kg	140 kg	140 kg



Features & Benefits:

- Foot Steel Frame
- Optional Contoured Padded Overlay
- Quick Release Solid 24" Rear Wheels
- Height Adjustable, 8" Castors
- Dacron Fire Retardant Fabric
- Swing-back Removable Armrests
- Push-to-lock Brakes
- Removable Swing Away Legrests (Elevating / Articulating optional accessory)
- Height Adjustable Footrest



Aspire Rehab RX Tilt in Space Wheelchair

Code	MWS449710	MWS449720	MWS449740
Seat Width	410 - 460 mm	460 - 510 mm	510 - 560 mm
Seat Depth	440 - 530 mm	440 - 530 mm	440 - 560 mm
Seat Height (Front)	410 - 440 mm	410 - 440 mm	410 - 440 mm
Seat Height (Rear)	400 - 475 mm	400 - 475 mm	400 - 475 mm
Overall Width	690 mm	740 mm	790 mm
Backrest Height	460 - 710 mm	460 - 710 mm	460 - 710 mm
Armrest Height	310 - 460 mm	310 - 460 mm	310 - 460 mm
SWL	180 kg	180 kg	180 kg

Features & Benefits:

- Attendant Operated Drum Brakes & Push-to-lock Handbrakes
- Removable, Height & Depth Adjustable Armrest
- Quick release, Height & Depth Adjustable Solid 24" Rear Wheels & Height Adjustable 6" Castors Adjustable, 8" Castors
- Tilt-in-Space Functionality
- Height, Depth, Angle & Width Adjustable Removable Headrest and Backrest
- Swing-away, Removable, Padded & Elevating Legrest
- Height & Angle Adjustable Footrest



Aspire Rehab RS Tilt in Space Wheelchair

Code	MWS449600	MWS449610	MWS449620
Seat Width	410 - 460 mm	410 - 460 mm	410 - 460 mm
Seat Depth	440 - 530 mm	440 - 530 mm	440 - 560 mm
Seat Height (Front)	410 - 440 mm	410 - 440 mm	410 - 440 mm
Seat Height (Rear)	400 - 475 mm	400 - 475 mm	400 - 475 mm
Overall Width	690 mm	740 mm	790 mm
Backrest Height	460 - 710 mm	460 - 710 mm	460 - 710 mm
Armrest Height	310 - 460 mm	310 - 460 mm	310 - 460 mm
SWL	180 kg	180 kg	180 kg

Features & Benefits:

- Attendant Operated Drum Brakes & Push-to-lock Handbrakes
- Removable, Height & Depth Adjustable Armrest
- Quick release, Height & Depth Adjustable Solid 24" Rear Wheels & Height Adjustable 6" Castors Adjustable, 8" Castors
- Tilt-in-Space Functionality
- Height, Depth, Angle & Width Adjustable Removable Headrest and Backrest
- Swing-away, Removable, Padded & Elevating Legrest
- Height & Angle Adjustable Footrest





Aspire Assist 2 Deluxe Vinyl Wheelchair

Code	MWS449340	MWS449350	MWS449360
Seat Width	350 mm	400 mm	450 mm
Seat Depth	400 mm	400 mm	400 mm
Seat Height	460 - 500 mm	460 - 500 mm	460 - 500 mm
Overall Width	350 mm	400 mm	450 mm
Backrest Height	440 mm	440 mm	440 mm
Armrest Height	210 mm	210 mm	210 mm
SWL	140 kg	140 kg	140 kg

Code	MWS449370	MWS449380 - HD	MWS449390 - HD
Seat Width	500 mm	570 mm	610 mm
Seat Depth	400 mm	400 mm	400 mm
Seat Height	460 - 500 mm	460 - 500 mm	460 - 500 mm
Overall Width	500 mm	570 mm	610 mm
Backrest Height	440 mm	440 mm	440 mm
Armrest Height	210 mm	210 mm	210 mm
SWL	140 kg	180 kg	180 kg



Features & Benefits:

- Infection control compliant
- Optional fixed frame
- Swing away and removable arm rests
- Height adjustable and removable foot rests
- Quick release 24" solid rear tyres - the wheels are easily removed to reduce the weight of the chair for transport and storage.



Aspire Rehab RX JNR Wheelchair

Code	MWS449630
Seat Width	320 - 370 mm
Seat Depth	440 - 490 mm
Seat Height (Front)	410 - 440 mm
Seat Height (Rear)	400 - 475 mm
Overall Width	600 mm
Backrest Height	460 - 710 mm
Armrest Height	310 - 460 mm
SWL	180 kg



Features & Benefits:

- Attendant Operated Drum Brakes & Push-to-lock Handbrakes
- Removable, Height & Depth Adjustable Armrest
- Tilt-in-Space Functionality
- Quick release, Height & Depth Adjustable Solid 20" Rear Wheels & Height Adjustable 6" Castors
- Height, Depth, Angle & Width Adjustable Removable Headrest
- Depth Adjustable Seat, Height & Depth Adjustable Backrest
- Swing-away, Removable, Padded & Elevating Legrest
- Height & Angle Adjustable Footrest



Action Folding Manual Wheelchair - Action 3 Lever Drive



Code	MWS442400	MWS442500	MWS442600
Description	Left Hand Drive	Right Hand Drive	Left Hand Drive
Seat Depth	410mm	410mm	410mm
Seat Width	410mm	410mm	440mm
Seat Height	400 - 500mm	400 - 500mm	400 - 500mm
Backrest Height	410mm	410mm	410mm
SWL	125kg	125kg	125kg

Code	MWS442700	MWS442800	MWS442900
Description	Right Hand Drive	Left Hand Drive	Right Hand Drive
Seat Depth	410mm	410mm	410mm
Seat Width	440mm	500mm	500mm
Seat Height	400 - 500mm	400 - 500mm	400 - 500mm
Backrest Height	410mm	410mm	410mm
SWL	125kg	125kg	125kg



Features & Benefits:

- Single arm propelled wheelchair for home or hospital use
- Push pull lever designed for users with adequate upper limb strength in one arm
- Folding frame for easy storage and transportation
- Swing-away detachable footrests and removable armrests
- 24" quick-release pneumatic rear wheels plus 8" front castors
- Durable steel construction, with a 14.2kg weight

Heavy Duty & Super HD Wheelchair

Code	MWS442910 - HD	MWS442911 - HD	MWS442912 - HD
Seat Depth	400 mm	450 mm	450 mm
Seat Width	500 mm	550 mm	600 mm
Seat Height	500 mm	500 mm	500 mm
Backrest Height	400 mm	400 mm	400 mm
SWL	136kg	204kg	204kg

Code	MWS442901 - Super HD	MWS442902 - Super HD
Seat Depth	500 mm	500 mm
Seat Width	650 mm	700 mm
Seat Height	500 mm	500 mm
Backrest Height	500 mm	500 mm
SWL	318kg	318kg



Features & Benefits:

- Reinforced wheelchair for bariatric users
- Extra wide seat widths and reinforced construction accommodates larger users
- Moulded composite mag wheels
- Swing-away detachable footrests and removable padded armrests



Breezy Basix 2 Manual Wheelchair

FIXED WHEELCHAIRS

Code	MWS449091	MWS449108
Seat Depth	410 - 460 mm	410 - 460 mm
Seat Width	360 mm	400 mm
Seat Height	425 - 510 mm	425 - 510 mm
Backrest Height	410 - 460 mm	410 - 460 mm
SWL	125 kg	125 kg

Code	MWS449114	MWS449097
Seat Depth	410 - 460 mm	410 - 460 mm
Seat Width	460 mm	520 mm
Seat Height	425 - 510 mm	425 - 510 mm
Backrest Height	410 - 460 mm	410 - 460 mm
SWL	125 kg	125 kg



Fixed Features & Benefits:

- Lightweight chair
- Available in self-propelled or transit
- Adjustable push handle height
- Tension adjustable backrest upholstery
- Swing away legrests as standard
- Drum break option available (16, 18 & 20")
- 41 - 46 cm adjustable seat depth
- Castor angle adjustment 0, 3 & 6 degrees

FOLDING WHEELCHAIRS

Code	MWS449104	MWS449111
Seat Depth	410 - 460 mm	410 - 460 mm
Seat Width	360 mm	400 mm
Seat Height	425 - 510 mm	425 - 510 mm
Backrest Height	410 - 460 mm	410 - 460 mm
SWL	125 kg	125 kg

Code	MWS449118	MWS449123
Seat Depth	410 - 460 mm	410 - 460 mm
Seat Width	460 mm	520 mm
Seat Height	425 - 510 mm	425 - 510 mm
Backrest Height	410 - 460 mm	410 - 460 mm
SWL	125 kg	125 kg



Folding Features & Benefits:

- Folding lightweight chair
- Available in self-propelled or transit
- Adjustable push handle height (+/- 3")
- Available with folding backrest
- Tension adjustable upholstery on backrest
- Swing away legrests as standard
- Drum break option available (16, 18 & 20")
- 41 - 46 cm adjustable seat depth
- Castor angle adjustment 0, 3 & 6 degrees



Quickie IRIS Tilt-in-Space Wheelchair

Code	MWC427130
Seat Width	355 - 560 mm
Seat Depth	355 - 560 mm
Seat Height	320 - 500 mm
Overall Width	240 mm
Backrest Height	380 - 530 mm / 460 - 610 mm
SWL	136 kg



Features & Benefits:

- 40° or 55° of Intelligent Rotation in Space Technology
- Rocker Arm Technology and Width Adjusting Struts
- JAY Lower Extremity Support
- Caregiver Options
- Intuitive Hanger Designs
- NEW MONO Backrest System



Quickie SR45 Manual Tilt Wheelchair

Code	MWC427131
Seat Width	360 - 510 mm
Seat Depth	360 - 510 mm
Seat Height	360 - 520 mm
Backrest Height	380 - 530 mm / 455 - 610 mm
SWL	136 kg



Features & Benefits:

- Proven Rotation-In-Space Technology
- Non folding back canes
- Height adjustable back with adjustable stroller handles
- Foot tilt
- Transit tie downs
- Dual post height adjustable flip back with full length arm pads
- 70° Swing in/ out hangers, solid seat pan and rear anti tips
- Composite foot plates



Cirrus G5 Manual Tilt Wheelchair

Code	MWC427132
Seat Width	420 - 540 mm
Seat Depth	390 - 550 mm
Seat Height	380 - 550 mm
Overall Width	Seat Width + 220mm (+240 mm with drum brake)
Backrest Height	550 - 650 mm
Seat Tilt	0° - 33°
Back Recline	0° - 35°
SWL	135 kg



Features & Benefits:

- 33° tilt and 35° backrest adjustment
- Easy to operate sliding seat for safe and easy transfer in and out of the tilt in space wheelchair
- Includes comfortable upholstery, flip up armrests and angle adjustable legrests



Quickie 2 Manual Folding Wheelchair

Code	MWC427230NSW1
Seat Width	120 - 220 mm
Seat Depth	120 - 200 mm
Seat Height	135 - 220 mm
Backrest Height	90 - 210 mm
Backrest Angle	-15° to +3°
Camber	0°, 2°, 4°
SWL	136 kg



Features & Benefits:

- Modular Frame Design
- Light & Durable Crossbrace
- Adjustable Axle Plate
- Integral Caster Housing
- EXO Upholstery
- Environmental Accessibility



Quickie 2 Lite Manual Folding Wheelchair

Code	MWC427235NSW1
Seat Width	140 - 200 mm
Seat Depth	140 - 200 mm
Seat Height	135 - 220 mm
Backrest Height	90 - 210 mm
Backrest Angle	-15° to +3°
Camber	0°, 2°, 4°
SWL	120 kg



Features & Benefits:

- Modular Frame Design
- Light & Durable Crossbrace
- Adjustable Axle Plate
- Integral Caster Housing
- EXO Upholstery
- Environmental Accessibility



Quickie 7R Series Manual Rigid Wheelchair

Code	MWC427296NSW1
Seat Width	120 - 200 mm
Seat Depth	120 - 200 mm
Front Seat Height	160 - 210 mm
Rear Seat Height	130 - 200 mm
Backrest Height	80 - 200 mm
SWL	120 kg



Features & Benefits:

- Freestyle Backrest System for Freedom of Movement providing a full range of upper body motion and lowering the overall weight of your wheelchair
- 3 caster settings, 2 frame lengths (per seat depth), 7 rear wheel options, and 9 rear tire options
- Thin, light tubing with strength and stiffness with a transport weight starting at 4.5kgs*
- 7 Series manual wheelchairs are Light and Mighty



Quickie 5R Series Manual Rigid Wheelchair

Code	MWC427297NSW1
Seat Width	120 - 200 mm
Seat Depth	120 - 200 mm
Front Seat Height	160 - 210 mm
Rear Seat Height	130 - 200 mm
Backrest Angle	Fore (-) 17° to Aft (+) 8° Front Seat
SWL	120 kg



Features & Benefits:

- Swept-back axle plate design. Available in two lengths - short (4.5" of vertical adjustment) and long (6" of vertical adjustment)
- 5R adjustable wheelchair offers premium options that can elevate your product
- Offers two manual wheelchair frame options. The Classic frame features a traditional frame length for maximum stability. The shortened Performance frame length offers maximum responsiveness



Quickie QXI Manual Rigid Wheelchair

Code	MWC427335NSW1
Seat Width	355 - 510 mm
Seat Depth	355 - 510 mm
Front Seat Height	320 - 495 mm
Rear Seat Height	305 - 480 mm
Back Height	130 - 200 mm
Backrest Angle	-15° - 3°
SWL	120 kg



Features & Benefits:

- Durable Frame Design
- Simple Serviceability
- Low Seat Heights - a 13" seat height can be achieved with 5" casters, which give you the ability to maneuver over thick carpet or outdoor obstacles
- Quickie QXi's new EXO upholstery boasts a modern and comfortable design



Quickie QRI Manual Rigid Wheelchair

Code	MWC427495NSW1
Seat Width	305 - 510 mm
Seat Depth	305 - 510 mm
Front Seat Height to Floor	380 - 510 mm
Rear Seat Height to Floor	355 - 510 mm
Backrest Angle	-8° to 17°
SWL	120 kg



Features & Benefits:

- Sturdy open frame features a stable wheelbase and fluid caster design
- QRI comes standard with 0" or 1" of frame inset, a highly adjustable axle plate for perfecting your Center-of-Gravity setting and multiple front frame angle options
- Top options such as; Folding Lock-Down Angle Adjustable Back and a wide range of seat widths, seat depths, armrests, wheels, tires and hand rims



Zippie IRIS Tilt-in-Space Folding Wheelchair

Code	MWC427500
Seat Width	254 - 406.4 mm
Seat Depth	254 - 457.2 mm
Front Seat Height	330.2 - 482.6 mm w/drop seat: 279.4 - 444.5 mm
Rear Seat Height	330.2 - 482.6 mm w/drop seat: 279.4 - 444.5 mm
Backrest Height	406.4 - 609.6 mm
Backrest Angle	Fore (-) 5° to Aft (+) 30°
SWL	135 kg



Features & Benefits:

- 40° or 55° of Intelligent Rotation in Space Technology
- Folding frame option offers up to 4" of built-in depth growth and 2" of built-in width growth
- The MONO Backrest System's single back post offers limitless seating and positioning capabilities
- Folding crossbrace fully locks when unfolded for superior rigidity, and folds into a compact size for convenient transport



Zippie Zone Manual Rigid Wheelchair

Code	MWC427487NSW1
Seat Width	200 - 405 mm
Seat Depth	200 - 460 mm
Front Seat Height	355 - 480 mm
Rear Seat Height	330 - 480 mm
Backrest Height	150 - 460 mm
Frame Angle	80°
SWL	75 kg



Features & Benefits:

- Growth Capabilities - 3" of depth growth built into frame + an extra 2" built into the sling upholstery
- Inset backrest, flip-up, angle adjustable footrest and hub lock located on the seat rail
- Ultra Lightweight Aerospace Aluminum



Zippie Xcape Manual Folding Wheelchair

Code	MWC427501NSW1
Seat Width	203.2 - 406.4 mm
Seat Depth	203.2 - 457.2 mm
Front Seat Height	330.2 - 282.6 mm
Rear Seat Height	330.2 - 279.4 mm
Frame Angle	80° (Z-finity™ System allows for infinite angle adjustment)
SWL	75 kg



Features & Benefits:

- Paediatric Specific Design - 2" of growth in the crossbrace and 3" in the seat rail keep your child positioned properly for maximum independence
- XLOCK Crossbrace for Performance and Convenience
- Rotating hardware allows for infinite adjustment of the footrest angle and placement to achieve optimal positioning of the feet, ankles, and knees



Quickie Xtender Power-Assist Wheelchair Add-on

Code	MWC427310
Max. Range	15 km - 27 km
Batteries	NiMH or Li Ion
Total Weight	17 kg
SWL	120 kg



Features & Benefits:

- Motorised wheels
- Automatic Wheel Synchronization
- Quick-Release Wheels and Easy Storage
- Rollback Prevention and Downhill Speed Control
- Range of Modes and Models



Quickie iXpress Power-Assist Wheelchair Add-on

Code	WCA858506
Max. Range	16 km per charge
Batteries	Nickel Metal Hydride
Total Weight	17.4 kg
SWL	120 kg



Features & Benefits:

- Selectable speeds for easy transitions between environments
- Easy to use ergonomic joystick controller
- Full function attendant control with innovative glide to steer function

Lite Drive Power-Assist Wheelchair Add-on

Code	WCA858512
Max. Range	14 -16 km
Batteries	Lithium
Total Weight	8.8 kg
SWL	120 kg



Features & Benefits:

- Motor attachment simply hooks onto the rear of most rigid or folding manual wheelchairs.
- Controlled by a joystick while maintaining the chair's manoeuvrability
- Switch between assisted power or manual use
- Rollback Prevention and Downhill Speed Control
- Range of Modes and Models



Power Wheelchairs



Quickie Xperience Mid Wheel Power Wheelchair

Code	PWC652005NSW3	PWC652005NSW6
Seat Width	279.4 - 609.6 mm	279.4 - 609.6 mm
Seat Depth	279.4 - 609.6 mm	279.4 - 609.6 mm
Backrest Height	304.8 - 558.8 mm	304.8 - 558.8 mm
Overall Width	593.725 mm (with Narrow Frame) 644.525 mm (with STD Frame)	593.725 mm (with Narrow Frame) 644.525 mm (with STD Frame)
Overall Length	892.175 mm (without Front Riggings)	892.175 mm (without Front Riggings)
Electronics	400.05 mm (without power seating) 406.4 mm (with Power Tilt)	400.05 mm (without power seating) 406.4 mm (with Power Tilt)
SWL	136 kg	136 kg



Features & Benefits:

- Includes interactive 6-wheel suspension and seat suspension which together enhance the stability, mobility and comfort for the user
- The unique suspension will distribute the weight over a larger footprint and improve the stability
- The independent suspension stabilizes the seat in downhill and uphill transitions to keep the user comfortable in their chair



Quickie Xplore Power Wheelchair

Code	PWC652015NSW4	PWC652015NSW7
Seat Width	279.4 - 609.6 mm	279.4 - 609.6 mm
Seat Depth	279.4 - 609.6 mm	279.4 - 609.6 mm
Backrest Height	304.8 - 558.8 mm	304.8 - 558.8 mm
Overall Width	593.725 mm (with Narrow Frame) 644.525 mm (with STD Frame)	593.725 mm (with Narrow Frame) 644.525 mm (with STD Frame)
Overall Length	911.225 mm (without Front Riggings)	911.225 mm (without Front Riggings)
SWL	136 kg	136 kg



Features & Benefits:

- Motorised wheels
- Automatic Wheel Synchronization
- Quick-Release Wheels and Easy Storage
- Rollback Prevention and Downhill Speed Control
- Range of Modes and Models
- Available with tilt, shear reduction, recline, lift, power ELR's and Power Center mount



Breezy P100 Mid Wheel Power Wheelchair

Code	PWC652213NSW1
Seat Width	400 - 450 mm
Seat Depth	400 mm
Overall Width	520 mm
Overall Length	1040 mm
Max. Speed	7.8km/h
SWL	120 kg



Features & Benefits:

- Includes an optional power or manual mobility solution
- Flip back arm rests
- Swing away & detachable footrests
- Half folding backrests
- Foldable & Compact
- Document pouch



Quickie Q300 Mid-Wheel SEDEO LITE Power Wheelchair

Code	PWC655280NSW1 (w/Sling Back)	PWC655290NSW2 (w/Padded Back)
Seat Width	385 - 510 mm	385 - 510 mm
Seat Depth	410 - 560 mm	410 - 560 mm
Backrest Height	460 - 510 mm	460 - 510 mm
Powered Recline	85° - 120°	85° - 120°
Manual Recline	90° - 120°	90° - 120°
Tilt Angle	30° / 50°	30° / 50°
Lift	300 mm	300 mm
Suspension	Drive Wheels, Basic	Drive Wheels, Basic
Motors	2 pole	2 pole
Speed	10 kph	10 kph
Batteries	40 Ah	40 Ah
Electronics	VR2	VR2
SWL	136 kg	136 kg



Features & Benefits:

- Easy to adjust
- Height adjustable back with optional comfort cushions
- Length compensating swing away legrests
- Flip back armrest
- Integrated headrest design
- Positioning elements & integrated seat rail

Quickie Q300 Rear-Wheel SEDEO LITE Power Wheelchair

Code	PWC655260NSW1 (w/Sling Back)	PWC655270NSW2 (w/Padded Back)
Seat Width	385 - 510 mm	385 - 510 mm
Seat Depth	410 - 560 mm	410 - 560 mm
Backrest Height	460 - 510 mm	460 - 510 mm
Powered Recline	85° - 120°	85° - 120°
Manual Recline	90° - 120°	90° - 120°
Tilt Angle	30° / 50°	30° / 50°
Lift	300 mm	300 mm
Suspension	Drive Wheels, Basic	Drive Wheels, Basic
Motors	2 pole	2 pole
Speed	10 kph	10 kph
Batteries	40 Ah	40 Ah
Electronics	VR2	VR2
SWL	136 kg	136 kg



Features & Benefits:

- Easy to adjust
- Height adjustable back with optional comfort cushions
- Length compensating swing away legrests
- Flip back armrest
- Integrated headrest design
- Positioning elements & integrated seat rail



Quickie Q400 Rear-Wheel SEDEO LITE Power Wheelchair



Features & Benefits:

- Easy to adjust
- Height adjustable back with optional comfort cushions
- Length compensating swing away legrests
- Flip back armrest
- Integrated headrest design
- Positioning elements & integrated seat rail

Code	PWC655300NSW1	PWC655300NSW2 (w/Tilt)
Seat Width	385 - 510 mm	385 - 510 mm
Seat Height	415 - 490 mm	415 - 490 mm
Seat Depth	410 - 560 mm	410 - 560 mm
Backrest Height	460 - 510 mm	460 - 510 mm
Overall Width	640 mm	640 mm
Overall Length	Max. 1190 mm	Max. 1190 mm
Speed	10 kph	10 kph
Battery Size	60 Ah, 72 Ah	60 Ah, 72 Ah
Max. Range	Max. 40 km (with 80 Ah batteries)	Max. 40 km (with 80 Ah batteries)
Back Recline	85° to 120°	85° to 120°
Turning Diameter	950 mm	950 mm
Max. Safe Slope	8°	8°
Max. Kerb Climb	80 mm (100 mm with kerb climber)	80 mm (100 mm with kerb climber)
Electronics	VR2, R-Net	VR2, R-Net
Min. Wheelchair Weight	130 kg	130 kg
SWL	136 kg	136 kg
Colours	Green, Orange, Black & Silver	Green, Orange, Black & Silver



Quickie Q400 Mid-Wheel SEDEO LITE Power Wheelchair



Features & Benefits:

- Easy to adjust
- Height adjustable back with optional comfort cushions
- Length compensating swing away legrests
- Flip back armrest
- Integrated headrest design
- Positioning elements & integrated seat rail

Code	PWC655300NSW9 (Attendant Control)	PWC655310NSW1	PWC655310NSW2 (w/Tilt)
Seat Width	385 - 560 mm	385 - 560 mm	385 - 560 mm
Seat Height	415 - 490 mm	415 - 490 mm	415 - 490 mm
Seat Depth	410 - 560 mm	410 - 560 mm	410 - 560 mm
Backrest Height	460 - 510 mm	460 - 510 mm	460 - 510 mm
Overall Width	610 - 620 mm	610 - 620 mm	610 - 620 mm
Overall Length	Max. 1130 mm	Max. 1130 mm	Max. 1130 mm
Speed	10 kph	10 kph	10 kph
Battery Size	60 Ah, 72 Ah	60 Ah, 72 Ah	60 Ah, 72 Ah
Max. Range	Max. 40 km (with 80 Ah batteries)	Max. 40 km (with 80 Ah batteries)	Max. 40 km (with 80 Ah batteries)
Back Recline	85° to 120°	85° to 120°	85° to 120°
Turning Diameter	560 - 630 mm	560 - 630 mm	560 - 630 mm
Max. Safe Slope	8°	8°	8°
Max. Kerb Climb	100 mm	100 mm	100 mm
Electronics	VR2, R-Net	R-Net	R-Net
Min. Wheelchair Weight	130 kg	130 kg	130 kg
SWL	136 kg	136 kg	136 kg
Colours	Green, Orange, Black & Silver	Green, Orange, Black & Silver	Green, Orange, Black & Silver



Quickie Q400 Front-Wheel SEDEO LITE Power Wheelchair



Features & Benefits:

- Easy to adjust
- Height adjustable back with optional comfort cushions
- Length compensating swing away legrests
- Flip back armrest
- Integrated headrest design
- Positioning elements & integrated seat rail

Code	PWC655320NSW1	PWC655320NSW2 (w/Tilt)
Seat Width	385 - 510 mm	385 - 510 mm
Seat Height	415 - 490 mm	415 - 490 mm
Seat Depth	410 - 560 mm	410 - 560 mm
Backrest Height	460 - 510 mm	460 - 510 mm
Overall Width	640 mm	640 mm
Overall Length	Max. 1190 mm	Max. 1190 mm
Speed	10 kph	10 kph
Battery Size	60 Ah, 72 Ah	60 Ah, 72 Ah
Max. Range	Max. 40 km (with 72 Ah batteries)	Max. 40 km (with 72 Ah batteries)
Back Recline	85° to 120°	85° to 120°
Turning Diameter	735 mm	735 mm
Max. Safe Slope	8°	8°
Max. Kerb Climb	70 mm	70 mm
Electronics	VR2, R-Net	VR2, R-Net
Min. Wheelchair Weight	130 kg	130 kg
SWL	136 kg	136 kg
Colours	Green, Orange, Black & Silver	Green, Orange, Black & Silver



Quickie Q500 Rear-Wheel SEDEO LITE Power Wheelchair



Features & Benefits:

- Tailored Seating
- Sedeo Pro Seating System
- Positioning elements
- Quick and easy to adjust

Code	PWC655330NSW4 (w/ Padded Back)	PWC655330NSW7 (w/ Back Canes)
Seat Width	380 - 560 mm	380 - 560 mm
Seat Height	415 - 490 mm	415 - 490 mm
Seat Depth	400 - 560 mm	400 - 560 mm
Backrest Height	440 - 560 mm	440 - 560 mm
Overall Width	640 mm	640 mm
Overall Length	Max. 1180 mm	Max. 1180 mm
Speed	6 kph high torque, 10 kph standard	6 kph high torque, 10 kph standard
Battery Size	60 Ah, 72 Ah (optional)	60 Ah, 72 Ah (optional)
Max. Range	Max. 40 km	Max. 40 km
Back Recline	90° to 150°	90° to 150°
Turning Diameter	950 mm	950 mm
Max. Safe Slope	10°	10°
Max. Kerb Climb	80 mm without (100 mm with kerb climber)	80 mm without (100 mm with kerb climber)
Electronics	VR2, R-Net Controller; lights & indicators	VR2, R-Net Controller; lights & indicators
SWL	160 kg	160 kg
Colours	Red, Blue, Green, Orange, White, Black & Silver	Red, Blue, Green, Orange, White, Black & Silver



Quickie Q500 Mid-Wheel SEDEO LITE Power Wheelchair



Features & Benefits:

- Easy to adjust
- Height adjustable back with optional comfort cushions
- Length compensating swing away legrests
- Flip back armrest
- Integrated headrest design
- Positioning elements & integrated seat rail

Code	PWC655340NSW6 (w/ Padded Back)	PWC655340NSW3 (w/ Back Canes)
Seat Width	385 - 510 mm	385 - 510 mm
Seat Height	415 - 490 mm	415 - 490 mm
Seat Depth	410 - 560 mm	410 - 560 mm
Backrest Height	460 - 510 mm	460 - 510 mm
Overall Width	610 - 620 mm	610 - 620 mm
Overall Length	Max. 1130 mm	Max. 1130 mm
Speed	6 kph high torque, 10 kph standard	6 kph high torque, 10 kph standard
Battery Size	60 Ah, 72 Ah	60 Ah, 72 Ah
Max. Range	Max. 40 km (with 72 Ah batteries)	Max. 40 km (with 72 Ah batteries)
Back Recline	85° to 120°	85° to 120°
Turning Diameter	560 - 630 mm	560 - 630 mm
Max. Safe Slope	8°	8°
Max. Kerb Climb	70 mm	70 mm
Electronics	VR2, R-Net	VR2, R-Net
Min. Wheelchair Weight	140 kg	140 kg
SWL	136 kg	136 kg
Colours	Red, Blue, Green, Orange, White, Black & Silver	Red, Blue, Green, Orange, White, Black & Silver



Quickie Q500 Front-Wheel SEDEO LITE Power Wheelchair



Features & Benefits:

- Easy to adjust
- Height adjustable back with optional comfort cushions
- Power centre mount legrests
- Anti-shear backrest incorporates 0 - 50 degrees of movement
- Integrated headrest design
- Positioning elements & integrated seat rail

Code	PWC655350NSW5 (w/ Padded Back)	PWC655350NSW8 (w/ Back Canes)
Seat Width	380 - 560 mm	380 - 560 mm
Seat Height	415 - 490 mm	415 - 490 mm
Seat Depth	400 - 560 mm	400 - 560 mm
Backrest Height	440 - 560 mm	440 - 560 mm
Overall Width	640 mm	640 mm
Overall Length	Max. 1340 mm	Max. 1340 mm
Speed	6 kph high torque, 10 kph standard	6 kph high torque, 10 kph standard
Battery Size	60 Ah, 72 Ah (optional)	60 Ah, 72 Ah (optional)
Max. Range	40 km	40 km
Back Recline	90° to 150°	90° to 150°
Turning Diameter	735 mm	735 mm
Max. Safe Slope	8°	8°
Max. Kerb Climb	70 mm	70 mm
Electronics	VR2, R-Net Controller; lights & indicators	VR2, R-Net Controller; lights & indicators
SWL	160 kg	160 kg
Colours	Red, Blue, Green, Orange, White, Black & Silver	Red, Blue, Green, Orange, White, Black & Silver



Quickie Q700 Rear-Wheel SEDEO LITE Power Wheelchair



Features & Benefits:

- Easy to adjust
- Anti-shear backrest
- Biometric repositioning
- Highly customizable
- Easy-entry system
- Seat coaching provides pressure relief reminders

Code	PWC655360NSW4 (w/Padded Back)	PWC655360NSW7 (w/Back Canes)
Seat Width	400 - 560 mm	400 - 560 mm
Seat Height	430 - 480 mm	430 - 480 mm
Seat Depth	400 - 560 mm	400 - 560 mm
Backrest Height	510 - 610 mm	510 - 610 mm
Overall Width	640 mm	640 mm
Overall Length	Max. 1180 -1370 mm	Max. 1180 -1370 mm
Speed	6 kph high torque, 10 kph standard	6 kph high torque, 10 kph standard
Battery Size	60 Ah, 72 Ah	60 Ah, 72 Ah
Max. Range	40 km	40 km
Back Recline	30° to 50°	30° to 50°
Turning Diameter	950 mm	950 mm
Max. Safe Slope	10°	10°
Max. Kerb Climb	100 mm with Kerb Climber / 80 mm without KC	100 mm with Kerb Climber / 80 mm without KC
Electronics	R-Net Controller; lights & indicators	R-Net Controller; lights & indicators
SWL	160 kg	160 kg
Colours	Red, Blue, Green, Orange, Black & White	Red, Blue, Green, Orange, Black & White



Quickie Q700 Mid-Wheel SEDEO LITE Power Wheelchair



Features & Benefits:

- Flip back armrest
- High comfortable
- Highly adjustable
- Anti-shear backrest
- Power elevating legrest
- Flexible back cushion
- Positioning elements

Code	PWC655370NSW3 (w/ Padded Back)	PWC655370NSW6 (w/ Back Canes)
Seat Width	380 - 560 mm	380 - 560 mm
Seat Height	415 - 490 mm	415 - 490 mm
Seat Depth	400 - 560 mm	400 - 560 mm
Backrest Height	440 - 560 mm	440 - 560 mm
Overall Width	620 - 700 mm	620 - 700 mm
Overall Length	Max. 1190 mm	Max. 1190 mm
Speed	6 kph high torque, 10 kph standard	6 kph high torque, 10 kph standard
Battery Size	60 Ah, 72 Ah (optional)	60 Ah, 72 Ah (optional)
Max. Range	Max. 40 km (with 80 Ah batteries)	Max. 40 km (with 80 Ah batteries)
Seat Tilt	30° / 50°	30° / 50°
Seat Recline	90° to 150°	90° to 150°
Back Recline	560 - 630 mm	560 - 630 mm
Turning Diameter	10°	10°
Max. Safe Slope	100 mm	100 mm
Max. Kerb Climb	R-Net Controller; lights & indicators	R-Net Controller; lights & indicators
Electronics	From 145 kg (including 60 Ah batteries)	From 145 kg (including 60 Ah batteries)
SWL	160 kg	160 kg
Colours	Red, Blue, Green, Orange, White, Black & Silver	Red, Blue, Green, Orange, White, Black & Silver



Quickie Q700-UP Mid-Wheel SEDEO ERGO SEATING Power Wheelchair



Features & Benefits:

- Anti-shear backrest
- Biometric repositioning
- Easy-entry system
- Seat coaching provides pressure relief reminders
- 90° center-mount footrest
- Adjustable to fit you

Code	PWC655375NSW3	PWC655376NSW6 (Back Canes w/ Adapter)
Seat Width	400 - 500 mm	400 - 500 mm
Seat Height	450 - 480 mm	450 - 480 mm
Seat Depth	400 - 540mm	400 - 540mm
Backrest Height	510 - 610 mm	510 - 610 mm
Overall Width	620 mm	620 mm
Overall Length	1070 mm	1070 mm
Speed	6 kph high torque, 10 kph standard	6 kph high torque, 10 kph standard
Battery Size	60 Ah, 72 Ah (Optional)	60 Ah, 72 Ah (Optional)
Turning Diameter	1000 mm	1000 mm
Max. Safe Slope	10°	10°
Max. Kerb Climb	100 mm	100 mm
Electronics	R-Net Controller; lights & indicators	R-Net Controller; lights & indicators
SWL	120 kg	120 kg
Colours	Red, Blue, Green, Orange, Black & White	Red, Blue, Green, Orange, Black & White



Quickie Q700 Front-Wheel SEDEO LITE Power Wheelchair



Features & Benefits:

- Flip back armrest
- High comfortable
- Highly adjustable
- Anti-shear backrest
- Power elevating legrest
- Flexible back cushion
- Positioning elements

Code	PWC655380NSW5 (w/ Padded Back)	PWC655380NSW8 (w/ Back Canes)
Seat Width	385 - 510 mm	385 - 510 mm
Seat Depth	410 - 560 mm	410 - 560 mm
Backrest Height	460 - 510 mm	460 - 510 mm
Powered Recline	85° - 120°	85° - 120°
Manual Recline	90° - 120°	90° - 120°
Tilt Angle	30° / 50°	30° / 50°
Lift	300 mm	300 mm
Suspension	All Wheels	All Wheels
Motors	4 pole	4 pole
Speed	8/10 kph	8/10 kph
Batteries	60 Ah / 72 Ah	60 Ah / 72 Ah
Electronics	R-Net Controller; lights & indicators	R-Net Controller; lights & indicators
SWL	120 kg	120 kg



Quickie Q700-UP Front-Wheel SEDEO ERGO SEATING Power Wheelchair



Features & Benefits:

- Improved pressure relief for those who may have limited ability to independently weight shift or have to sit for long periods
- Enhanced function and ability to reach and access your environment
- Improved range of motion
- Supporting vital organ capacity including pulmonary, bowel and bladder function and improves circulation
- Promoting bone health and reducing the occurrence of skeletal deformities by encouraging standing
- Reduces abnormal muscle tone

Code	PWC655385NSW5	PWC655386NSW8 (Back Canes w/ Adapter)
Seat Width	400 - 500 mm	400 - 500 mm
Seat Height	450 - 480 mm	450 - 480 mm
Seat Depth	400 - 540mm	400 - 540mm
Backrest Height	510 - 610 mm	510 - 610 mm
Overall Width	620 mm	620 mm
Overall Length	1070 mm	1070 mm
Speed	6 kph high torque, 10 kph standard	6 kph high torque, 10 kph standard
Battery Size	60 Ah, 72 Ah (Optional)	60 Ah, 72 Ah (Optional)
Turning Diameter	1096 mm	1096 mm
Max. Safe Slope	8°	8°
Max. Kerb Climb	70 mm	70 mm
Electronics	R-Net Controller; lights & indicators	R-Net Controller; lights & indicators
Min. Wheelchair Weight	From 160 kg (including 60 Ah batteries)	From 160 kg (including 60 Ah batteries)
SWL	120 kg	120 kg
Colours	Red, Blue, Green, Orange, Black & White	Red, Blue, Green, Orange, Black & White

Wheelchair Accessories



Aspire Contoured Padded Overlay

- Offers the user increased comfort and is ideal for those who are in their wheelchair for longer periods of time
- Suits Aspire wheelchairs as well as many other brands within the market

Code	Description
WCA848330	350 mm
WCA848340	400 mm
WCA848350	450 mm
WCA848360	500 mm
WCA848370	570 mm
WCA848380	610 mm



Aspire Articulating Elevating Legrests

- Padded legrests mirror the anatomical range of movement of the knee joint, ensuring thighs don't elevate as legs are raised

Code	Description
WCA848160	Left - 300/320/350/400/410 mm
WCA848170	Right - 300/320/350/400/410 mm
WCA848180	Left - 450/460/500/510 mm
WCA848190	Right - 450/460/500/510 mm
WCA848200	Left - 570/610 mm
WCA848210	Right - 570/610 mm



Aspire Elevating Legrest

- Elevating padded legrests for improved user comfort

Code	Description
WCA848100	Left - 300/320/350/400/410 mm
WCA848110	Right - 300/320/350/400/410 mm
WCA848120	Left - 450/460/500/510 mm
WCA848130	Right - 450/460/500/510 mm
WCA848140	Left - 570/610 mm
WCA848150	Right - 570/610 mm



Aspire Stump Support

- For Amputee Support

Code	Description
WCA848220	Left - 300/320/350/400/450 mm
WCA848230	Right - 300/320/350/400/450 mm
WCA848240	Left - 500/550/570/610 mm
WCA848250	Right - 500/550/570/610 mm



Aspire Safety Lap Belt

- Suitable for supporting users with low tone or weakness
- Metal push button for secure fit

Code	Description
WCA848300	Metal Seatbelt Buckle



Aspire Oxygen Bottle Holder

- Holds oxygen bottle in place
- Designed to hold C size bottles

Code	Description
WCA848290	Oxygen Bottle Holder



Aspire Calf Strap

- Provides extra support for users calves

Code	Description
WCA848580	Calf Strap



Aspire IV Pole

- Facilitates intravenous infusion

Code	Description
WCA848280	IV Pole



Aspire Anti-tip Bars

- Ensures chair does not tilt over when traveling across inclines and uneven surfaces

Code	Description
WCA848270	Anti-Tip Bars



Aspire Evoke Headrest

- Wheelchair Head Rest suitable for the Aspire EVOKE - Complete Kit

Code	Description
WCA858467	Head Rest - Complete Kit



Seat Belt

- 2" Dual Adjustable Squeeze
- Black , Padded

Code	Description
WCA858175	Seat Belt 2"



Heavy Duty Stump Support

- Fits the Super Heavy Duty Wheelchair

Code	Description
WCA858009	26-30in - Left
WCA858010	26-30in - Right



Aidacare have a range of Product Application Guides available for the following areas:





Wheelchair Backrests



JAY - J3 Backrest

The Jay-J3 series of backrests are highly customisable to suit your client's needs.

Customisations cover 5 spectrums: (1) Contour Depth; (2) Level of Support; (3) Back Support Height; (4) Backrest Width; (5) Mounting Hardware.

Various options within each spectrum create an enormously flexible package.

We strongly recommend that you consult with your Aidacare Complex Rehab team member for any inquiries relating to these cushions.



JAY




- The J3 Back is dedicated to eliminating compromises when different products are bundled. J3 ensures compatibility between solutions by encompassing a huge array of options within the one range
- The J3 Back features one of the widest ranges of available accessories including multiple lateral sizes, Spine-Align positioning components, Whitmyer® headrests, Comfort Fit® chest straps and trunk straps
- Every J3 back features special new spacer fabric upholstery designed to wick moisture away from the skin and circulate air flow throughout the cover
- 135 kg capacity on standard models and 225 kg in models over 22"
- The J3 back provides up to 22° of back angle adjustment with minimal to zero loss of seat depth. This is especially helpful for individuals with postural deformities who may require more extreme angles
- Fitting the back to the user not the user to the back is the goal of the Spine-Align Posture Conforming system. This is accomplished by combining a wide range of individual foam components to create unique shapes that optimise postural support, evenly distribute pressure and maximise function. Velcro strips attach to each shape so they can be placed into hundreds of configurations. The flexibility of the system is endless



J3 Contour Depth Profile



J3 Range of Trunk Support





JAY J3 Backrest

Description	Code
Posterior Deep Upper Thoracic Med 14in	PTB533696
Posterior Deep Upper Thoracic Med 16in	PTB533697
Posterior Deep Upper Thoracic Med 18in	PTB533698
Posterior Deep Contour Lower Thoracic Med 18in	PTB533854
Posterior - Upper Thoracic Medium 12in	PTB533843
Posterior Deep Upper Thoracic Med 20in	PTB533699
Posterior - Lower Thoracic Small 14in	PTB533700
Posterior - Lower Thoracic Small 16in	PTB533701
Posterior - Lower Thoracic Small 18in	PTB533702
Posterior - Lower Thoracic Med 14in	PTB533703
Posterior - Lower Thoracic Med 16in	PTB533704
Posterior - Lower Thoracic Med 18in	PTB533705
Posterior - Lower Thoracic Tall 14in	PTB533706
Posterior - Lower Thoracic Tall 16in	PTB533707
Posterior - Lower Thoracic Tall 18in	PTB533708
Posterior - Lower Thoracic Tall 20in	PTB533709
Posterior - Shoulder Height Small 16in	PTB533770
Posterior - Shoulder Height Small 14in	PTB533769
Posterior - Shoulder Height Small 18in	PTB533771
Posterior - Shoulder Height Small 20in	PTB533772
Posterior - Shoulder Height Med 16in	PTB532832
Posterior - Shoulder Height Med 16in	PTB533773
Posterior - Shoulder Height Med 18in	PTB533774
Posterior - Shoulder Height Med 20in	PTB533775
Posterior - Shoulder Height Tall 18in	PTB533776
Posterior - Shoulder Height Tall 20in	PTB533777
Posterior & Lateral - Shoulder Height Small 18in	PTB533780
Posterior & Lateral - Shoulder Height Small 14in	PTB533778
Posterior & Lateral - Shoulder Height Small 16in	PTB533779
Posterior & Lateral - Shoulder Height Medium 16in	PTB533794
Posterior & Lateral - Shoulder Height Medium 18in	PTB533795

JAY J3 Backrest

Description	Code
Posterior & Lateral - Shoulder Height Tall 18in	PTB533797
Posterior - Mid Thoracic Small 14in	PTB533710
Posterior - Mid Thoracic Small 16in	PTB533711
Posterior - Mid Thoracic Small 18in	PTB533712
Posterior - Mid Thoracic Small 20in	PTB533713
Posterior - Mid Thoracic Med 14in	PTB533714
Posterior - Mid Thoracic Med 16in	PTB533715
Posterior - Mid Thoracic Med 18in	PTB533716
Posterior - Mid Thoracic Med 20in	PTB533717
Posterior - Mid Thoracic Tall 14in	PTB533718
Posterior - Mid Thoracic Tall 16in	PTB533719
Posterior - Mid Thoracic Tall 18in	PTB533720
Posterior - Mid Thoracic Tall 20in	PTB533721
Posterior & Deep Contour Shoulder Height Small 16in	PTB533684
Posterior & Deep Contour Shoulder Height Small 18in	PTB533685
Posterior & Deep Contour Shoulder Height Small 20in	PTB533686
Posterior & Deep Contour Lateral Med 18in	PTB533687
Posterior & Deep Contour Mid Thoracic Tall 14in	PTB533683
Posterior & Deep Contour - Mid Thoracic Tall 16in	PTB533695
Posterior & Deep Contour Upper Thoracic Med 16in	PTB533681
Posterior & Deep Contour - Upper Thoracic Med 18in	PTB533682
Posterior & Deep Lateral - Shoulder Height Short 22in	PTB533791
Posterior & Deep Lateral - Shoulder Height Small 20in	PTB533785
Posterior & Deep Lateral - Shoulder Height Small 14in	PTB533782
Posterior & Deep Lateral - Shoulder Height Small 16in	PTB533783
Posterior & Deep Lateral - Shoulder Height Small 18in	PTB533784
Posterior & Deep Lateral - Shoulder Height Med 16in	PTB533786
Posterior & Deep Lateral - Shoulder Height Med 18in	PTB533787
Posterior & Deep Lateral - Shoulder Height Med 20in	PTB533788
Posterior & Deep Lateral - Shoulder Height Med 20in	PTB533781
Posterior & Deep Lateral - Shoulder Height Tall 18in	PTB533789





JAY J3 Backrest

Description	Code
Posterior & Deep Lateral - Shoulder Height Tall 20in	PTB533790
Posterior & Deep Lateral - Upper Thoracic Small 14in	PTB533757
Posterior & Deep Lateral - Upper Thoracic Small 16in	PTB533758
Posterior & Deep Lateral - Upper Thoracic Small 18in	PTB533759
Posterior & Deep Lateral - Upper Thoracic Small 20in	PTB533760
Posterior & Deep Lateral - Upper Thoracic Med 14in	PTB533761
Posterior & Deep Lateral - Upper Thoracic Med 16in	PTB533762
Posterior & Deep Lateral - Upper Thoracic Med 18in	PTB533763
Posterior & Deep Lateral - Upper Thoracic Med 20in	PTB533764
Posterior & Deep Lateral - Upper Thoracic Tall 14in	PTB533765
Posterior & Deep Lateral - Upper Thoracic Tall 16in	PTB533766
Posterior & Deep Lateral - Upper Thoracic Tall 18in	PTB533767
Posterior & Deep Lateral - Upper Thoracic Tall 20in	PTB533768
Posterior & Lateral - Mid Thoracic Small 20in	PTB533725
Posterior & Lateral - Mid Thoracic Small 12in	PTB533842
Posterior & Lateral - Mid Thoracic Small 14in	PTB533722
Posterior & Lateral - Mid Thoracic Small 16in	PTB533723
Posterior & Lateral - Mid Thoracic Small 18in	PTB533724
Posterior & Lateral - Mid Thoracic Medium 12in	PTB533798
Posterior & Lateral - Mid Thoracic Medium 14in	PTB533726
Posterior & Lateral - Mid Thoracic Medium 16in	PTB533727
Posterior & Lateral - Mid Thoracic Medium 18in	PTB533728
Posterior & Lateral - Mid Thoracic Medium 20in	PTB533729
Posterior & Lateral - Mid Thoracic Tall 14in	PTB533730
Posterior & Lateral - Mid Thoracic Tall 16in	PTB533731
Posterior & Lateral - Mid Thoracic Tall 18in	PTB533732
Posterior & Lateral - Mid Thoracic Tall 20in	PTB533733
Posterior & Lateral - Upper Thoracic Small 12in	PTB533690
Posterior & Lateral - Upper Thoracic Small 14in	PTB533746
Posterior & Lateral - Upper Thoracic Small 16in	PTB533747
Posterior & Lateral - Upper Thoracic Small 18in	PTB533748

JAY J3 Backrest

Description	Code
Posterior & Lateral - Upper Thoracic Medium 14in	PTB533749
Posterior & Lateral - Upper Thoracic Medium 16in	PTB533750
Posterior & Lateral - Upper Thoracic Medium 18in	PTB533751
Posterior & Lateral - Upper Thoracic Medium 20in	PTB533752
Posterior & Lateral - Upper Thoracic Tall 14in	PTB533753
Posterior & Lateral - Upper Thoracic Tall 16in	PTB533754
Posterior & Lateral - Upper Thoracic Tall 18in	PTB533755
Posterior & Lateral - Upper Thoracic Tall 18in	PTB533849
Posterior & Lateral - Upper Thoracic Tall 20in	PTB533756
Posterior - Upper Thoracic Small 14in	PTB533734
Posterior - Upper Thoracic Small 16in	PTB533735
Posterior - Upper Thoracic Small 18in	PTB533736
Posterior - Upper Thoracic Small 20in	PTB533737
Posterior - Upper Thoracic Medium 14in	PTB533738
Posterior - Upper Thoracic Medium 16in	PTB533739
Posterior - Upper Thoracic Medium 18in	PTB533740
Posterior - Upper Thoracic Medium 20in	PTB533741
Posterior - Upper Thoracic Tall 14in	PTB533742
Posterior - Upper Thoracic Tall 16in	PTB533743
Posterior - Upper Thoracic Tall 18in	PTB533744
Posterior - Upper Thoracic Tall 20in	PTB533745
Posterior & Deep Lateral - Shoulder Height Short 20in	PTB533792
Posterior & Deep Lateral - Shoulder Height Small 20in	PTB533785
Posterior & Deep Lateral - Shoulder Height Med 20in	PTB533788
Posterior & Deep Lateral - Shoulder Height Tall 20in	PTB533790
Posterior & Deep Lateral - Upper Thoracic Small 20in	PTB533760
Posterior & Deep Lateral - Upper Thoracic Med 20in	PTB533764
Posterior & Deep Lateral - Upper Thoracic Tall 20in	PTB533768



Product brochures also available!

Please contact us for a copy



Pediatric



Zippie Voyage Stroller

Code	PED478197
Seat Width	VAS: 152.4 to 330.2 mm VMS: 241.3 to 304.8 mm
Seat Depth	VAS: 127 to 330.2 mm VMS: 203.2 to 330.2 mm
Backrest Height	177.8 - 431.8 mm
Backrest Recline	100° (80° to 180°)
Seat Tilt	35° (-5° to 30°)
Seat Height	596.9 – 673.1 (3 steps possible 596.9 / 635 / 673.1)
Lower Leg Length	152.4 – 317.5 mm
Overall Width	635 mm
Overall Length	1117.6 mm
Total Weight	18 kgs (12kgs Base & 6kgs seating)
SWL	34 kg



Features & Benefits:

- Slide-N-Lock Interface Plate
- Offers 35° of rearward tilt and an optional 45° of recline assist with feeding, digestion, respiratory function, and visual orientation
- Reversible Seat with Tilt and Recline



1300 133 120
www.aidacare.com.au

