



# WHEELCHAIR RANGE

aspire for...

Comfort

Posture

Mobility



EVOKE 2



REHAB RX



ASSIST 2



TRANSIT 2



LITE TRANSIT



[www.aspirecare.com.au](http://www.aspirecare.com.au)  
1300 133 120





# aspire EVOKE 2 *Lightweight & Highly Adjustable*

The Aspire EVOKE 2 and EVOKE 2 HD are highly adjustable, lightweight, aluminium wheelchairs designed to enable a personalised fit for every user. A comprehensive range of compatible accessories is available for increased independence and enhanced clinical outcomes.




## FEATURES

- Frame:** Folding Lightweight Aluminium
- Legrest:** Swing-away & Removable
- Footrest:** Height & Angle Adjustable
- Armrest:** Swing-back & Removable
- Wheels:** Quick Release, Solid 24" Tyres, Height & Depth Adjustable
- Castors:** 8", Height & Angle Adjustable
- Brakes:** Easy Access Push-to-Lock Brakes
- Seat:** Depth & Height Adjustable
- Backrest:** Height, Tension, Angle & Depth Adjustable
- Upholstery:** Dacron Fire Retardant Fabric
- Cushion:** Contoured Overlay is optional, Standard cushion Included
- Weight:** From 14.8kg (SWL 140kg - HD 180kg)



**OPTIONAL CONTOURED PADDED OVERLAY**  
This offers the user increased comfort and is ideal for those who are in their wheelchair for longer periods of time. The contouring assists in positioning and pressure distribution, while the fabric allows air movement, increasing breathability. It is easily removed for washing.



## CUSTOMISABLE BACKREST

- ✓ Tension Adjustable
- ✓ Angle Adjustable
- ✓ Height Adjustable

**2**  
Year  
Warranty  
Frame


**1**  
Year  
Warranty  
Components

**S.W.L**  
**140kg**

**S.W.L**  
**180kg (HD)**

- ✓ DVA Contracted
- ✓ AS / NZS Approved
- ✓ Evoke is registered in the ARTG, AUST R ARTG 291670

- OPTIONAL ACCESSORIES**
- Elevating Legrest
  - Brake Extensions
  - Anti-tip Bars
  - Headrest Assembly
  - Advanced Articulating Elevating Legrest
  - Lateral Supports
  - IV Pole
  - Extended Back Canes 18" - 21"
  - Stump Supports
  - Contoured Padded Overlay
  - Safety Belt
  - Camber Kit
  - Oxygen Bottle Holder
  - Gutter Arm Rests\*
  - Calf Straps
  - Drum Brakes



| SEAT WIDTH   | CODE                         |
|--------------|------------------------------|
| 350 mm (14") | MWS449500                    |
| 400 mm (16") | MWS449510                    |
| 450 mm (18") | MWS449520                    |
| 500 mm (20") | MWS449530                    |
| 570 mm (22") | MWS449540 (HEAVY DUTY model) |
| 610 mm (24") | MWS449550 (HEAVY DUTY model) |

\*For Detailed Features, Specifications and Accessories see pages 14 - 20 \*Note: Side transfers are not possible when gutter armrests are attached

Aspire EVOKE 2 is crash tested to AS/NZS3696:19




# aspire EVOKE 2 JNR

All the adjustable features of the EVOKE 2 have been reduced in size to suit the unique needs of children, including smaller 16 inch rear wheels.

## CUSTOMISABLE BACKREST


- ✓ Depth Adjustable
- ✓ Angle Adjustable
- ✓ Height Adjustable



SEAT & BACKREST HEIGHT ADJUSTABLE

SEAT & BACKREST DEPTH ADJUSTABLE

BACKREST ANGLE ADJUSTABLE



## FEATURES

- Frame:** Folding Lightweight Aluminium
- Legrest:** Swing-away & Removable
- Footrest:** Height & Angle Adjustable
- Armrest:** Height Adjustable & Removable
- Wheels:** Quick Release, Solid 20" Tyres
- Castors:** 8", Height & Angle Adjustable
- Brakes:** Easy Access Push-to-lock
- Seat:** Height & Depth Adjustable
- Backrest:** Height, Angle & Depth Adjustable
- Upholstery:** Contoured Overlay is Optional, Standard Cushion Included
- Cushion:** Included
- Weight:** From 14kg

\*For Detailed Features, Specifications and Accessories see pages 14 - 20



2 Year Warranty Frame

1 Year Warranty Components

S.W.L 140kg

AS / NZS Approved

Evoke JNR is registered in the ARTG, AUST R ARTG 291670

| SEAT WIDTH   | CODE      |
|--------------|-----------|
| 300 mm (12") | MWS449560 |

Aspire EVOKE 2 JNR is crash tested to AS/NZS3696.19


# aspire REHAB RX JNR

The Aspire REHAB RX JNR is designed for advanced postural support and pressure care for children via easy repositioning and advanced adjustability.

**ADVANCED COMFORT**  
Breathable PU coated multi-stretch fabric on seat and back cushions ensure optimal skin microclimate, comfort and improve pressure care outcomes.

**TILT-IN-SPACE (TIS)**  
Functionality promotes increased comfort and improved positioning. As well as this, it allows body weight redistribution to help alleviate pressure areas.


**CUSHIONING**  
Multi-layer, castellated seat and back cushions with internal postural reinforcement optimise comfort and positioning.



BACKREST HEIGHT ADJUSTABLE



TILT-IN-SPACE FUNCTION



26° TILT  
30° RECLINE

ELEVATING LEGRESTS



SEAT & BACKREST DEPTH ADJUSTABLE



## FEATURES

- Frame:** Rigid Steel
- Legrest:** Swing-away, Removable, Padded & Elevating
- Footrest:** Height & Angle Adjustable
- Armrest:** Removable, Height & Depth Adjustable
- Wheels:** Quick Release, Solid 20" Tyres, Height & Depth Adjustable
- Castors:** 6", Height Adjustable
- Brakes:** Attendant Operated Drum Brakes & Push-to-lock Handbrakes
- Seat:** Depth & Width Adjustable
- Backrest:** Height, Tension & Angle Adjustable
- Headrest:** Height, Depth, Angle & Width Adjustable, Removable
- Upholstery:** PU Breathable Multi-stretch Fabric Covers
- Cushion:** Multilayer Castellated Back & Seat Cushions in Breathable PU
- Weight:** From 39.5kg

\*For Detailed Features, Specifications and Accessories see pages 14 - 20

| SEAT WIDTH               | CODE      |
|--------------------------|-----------|
| 320 - 370 mm (13" - 15") | MWS449630 |

Aspire REHAB RX JNR is crash tested to AS/NZS3696.19

AS / NZS Approved

Rehab RX JNR is registered in the ARTG, AUST R ARTG 291393

S.W.L 180kg

2 Year Warranty Frame

1 Year Warranty Components





# aspire REHAB RX *Advanced Tilt-In-Space*

The REHAB RX is geared towards the high needs, rehabilitation environment. Highly configurable and with pressure care cushioning surfaces, the REHAB RX is designed for the user with more complex needs.



## FEATURES

- Frame:** Rigid Steel Frame
- Legrest:** Swing-away, Removable, Padded & Elevating
- Footrest:** Height & Angle Adjustable
- Armrest:** Removable, Height & Depth Adjustable
- Wheels:** Quick Release, Solid 24" Tyres, Height & Depth Adjustable
- Castors:** 6", Height Adjustable
- Brakes:** Attendant Operated Drum Brakes & Push-to-lock Handbrakes
- Seat:** Depth, Width & Height Adjustable
- Backrest:** Height, Tension & Angle Adjustable
- Headrest:** Height, Depth, Angle & Width Adjustable, Removable
- Upholstery:** PU Breathable Multi-Stretch Fabric Covers
- Cushion:** Multilayer Castellated Back and Seat Cushion Covered in Breathable PU Fabric
- Weight:** From 41kg

\*For Detailed Features, Specifications and Accessories see pages 14 - 20



**SUPPORT SURFACES:**

- Multi-layer foam construction with castellated top layer for enhanced comfort, pressure redistribution and durability
- Breathable PU multi-stretch cover for improved pressure redistribution and skin micro-climate management

**BACKREST - CONTOURED:**

- Gentle lumbar build up for postural support
- Moderate lateral supports for assisted midline sitting

**CUSHION:**

- Integrated positioning skeleton for enhanced sitting posture
- Fabric tensioners provide a smooth support surface
- Gentle abductor and adductor contouring provide improved postural support

**ADJUSTABLE ELEVATING LEGRESTS**  
Elevating legrests with height & angle adjustable footrests.

**INFECTION CONTROL**  
Easy to clean surfaces.

**CUSTOM COMFORT**  
After-market backrests & cushions ensure flexibility.

**SAFETY IN DESIGN**  
Padded fittings and supports keep the user safe and secure at all times.

Aspire REHAB RX is crash tested to AS/NZS3696.19

**S.W.L 180kg**

**2 Year Warranty Frame**

**1 Year Warranty Components**

## THE HIGHLY ADJUSTABLE FEATURES FULFILL MANY CLINICAL REQUIREMENTS GEARED TOWARDS COMFORT AND SUPPORT

**OPTIONAL ACCESSORIES**  
A wide range of accessories to meet clinical needs

- Base Frame Extension
- 20" or 16" Alternative Wheels
- Therapist Adjustment Kit
- Stump Supports
- Safety Belt
- Oxygen Bottle Holder
- Meal Tray
- Anti-tip Bars
- IV pole

**BACKREST HEIGHT ADJUSTABLE**

**SEAT DEPTH ADJUSTABLE**

**ELEVATING LEGRESTS**

**HIGH LEVEL REHABILITATION SOLUTION**

Tilt-In-Space (TIS) functionality promotes increased comfort and improved positioning. As well as this, it allows body weight redistribution to help alleviate pressure areas.

**26° TILT**

**30° RECLINE**

| SEAT WIDTH               | CODE      |
|--------------------------|-----------|
| 410 - 460 mm (16" - 18") | MWS449710 |
| 460 - 510 mm (18" - 20") | MWS449720 |
| 510 - 560 mm (20" - 22") | MWS449740 |

Rehab RX is registered in the ARTG, AUST R ARTG 291393

DVA Contracted

AS / NZS Approved



# aspire REHAB RS Classic Tilt-In-Space

The REHAB RS is an ideal solution for Aged Care and Community users who requires increased postural support and bodyweight redistribution. A reclined position is easily achieved, making the REHAB RS also a great option for those who fatigue easily.



## FEATURES

- Frame:** Rigid Steel Frame
- Legrest:** Swing-away, Removable, Padded & Elevating
- Footrest:** Height & Angle Adjustable
- Armrest:** Removable, Height & Depth Adjustable
- Wheels:** Quick Release, Solid 24" Tyres, Height & Depth Adjustable
- Castors:** 6", Height Adjustable
- Brakes:** Attendant Operated Drum Brakes & Push-to-lock Handbrakes
- Seat:** Depth, Width & Height Adjustable
- Backrest:** Height, Tension & Angle Adjustable
- Headrest:** Height, Depth, Angle & Width Adjustable, Removable
- Upholstery:** PU Breathable Multi-Stretch Fabric Covers
- Cushion:** Standard Foam Comfort Cushions on Back & Seat
- Weight:** From 40.7kg


\*For Detailed Features, Specifications and Accessories see pages 14 - 20

## THE HIGHLY ADJUSTABLE FEATURES FULFILL MANY CLINICAL REQUIREMENTS GEARED TOWARDS COMFORT AND SUPPORT

### OPTIONAL ACCESSORIES

A wide range of accessories to meet clinical needs

- Base Frame Extension
- 20" or 16" Alternative Wheels
- Therapist Adjustment Kit
- Stump Supports
- Safety Belt
- Oxygen Bottle Holder
- Meal Tray
- Anti-tip Bars
- IV pole



BACKREST HEIGHT ADJUSTABLE




SEAT DEPTH ADJUSTABLE



ELEVATING LEGRESTS

### ★ LOW TO MEDIUM LEVEL REHABILITATION SOLUTION

Tilt-In-Space (TIS) functionality promotes increased support and improved positioning. This allows caregivers to position the user for optimal comfort. Adjustable, elevating legrests allow for precise leg positioning.



### INCREASED HEAD SUPPORT


The easy-to-adjust, supportive headrest offers the user superior head support, while the gently contoured backrest facilitates posture and positioning.

### SUPPORTIVE & COMFORTABLE

Padded armrests, elevating legrests & a supportive headrest ensure that users of the REHAB RS are supported and comfortable.

### ADVANCED COMFORT

Breathable PU coated multi-stretch fabric on seat and back cushions ensure optimal skin microclimate, comfort and improve pressure care outcomes.




### EASY TO CLEAN

Wipe clean surfaces ensure infection control compliance.



### SAFETY AT ITS CORE

Padded armrests, elevating legrests & a supportive headrest ensure that users of the REHAB RS remain safe and secure.



Aspire REHAB RS is crash tested to AS/NZS3696.19



| SEAT WIDTH               | CODE      |
|--------------------------|-----------|
| 410 - 460 mm (16" - 18") | MWS449600 |
| 460 - 510 mm (18" - 20") | MWS449610 |
| 510 - 560 mm (20" - 22") | MWS449620 |

- ✓ Rehab RS is registered in the ARTG, AUST R ARTG 291393
- ✓ DVA Contracted
- ✓ AS / NZS Approved



# aspire ASSIST 2 *Everyday*

The Aspire ASSIST 2 is a versatile and robust self-propelling wheelchair, designed to meet the rigorous demands of Community, Hire, Hospital and Aged Care environments. The Aspire ASSIST 2 is a reliable and comfortable solution with various accessories available to suit the needs of individuals and caregivers alike.



### FEATURES

- Frame:** Folding Steel Frame
- Legrest:** Swing-away, Removable, (Elevating optional accessory)
- Footrest:** Height Adjustable
- Armrest:** Swing-back, Removable
- Wheels:** Quick Release, Solid 24" Tyres
- Castors:** 8", Height Adjustable
- Brakes:** Push-to-lock
- Seat:** Fixed, Light Padding
- Backrest:** Fixed, Light Padding
- Upholstery:** Dacron Fire Retardant Fabric
- Cushion:** Optional Accessory
- Weight:** From 17.3kg

### ROBUST & RELIABLE

With a strong steel frame, removable swing-away legrests and quick release self-propelling rear wheels, the Aspire ASSIST 2 is a practical yet robust patient transport solution.

### CATERS TO A WIDE VARIETY OF ENVIRONMENTS

The large, puncture-proof wheels ensure that the Aspire ASSIST 2 handles varied terrain with ease.

### LOW MAINTENANCE FOLDING

Solid rear tyres and a centre cross brace design offer a low maintenance and portable mobility solution within a facility, hire or community environment.

| SEAT WIDTH   | CODE      |
|--------------|-----------|
| 350 mm (14") | MWS449300 |
| 400 mm (16") | MWS449310 |
| 450 mm (18") | MWS449320 |
| 500 mm (20") | MWS449330 |



- DVA Contracted
- AS / NZS Approved
- Assist 2 is registered in the ARTG, AUST R ARTG 291670

\*For Detailed Features, Specifications and Accessories see pages 14 - 20



# aspire ASSIST 2 *WARD*

The Aspire ASSIST 2 WARD Vinyl wheelchair has all the features of the ASSIST 2, but with durable hospital grade vinyl, suitable for the hospital & clinic environment. The ASSIST 2 WARD Vinyl has been carefully designed with fully welded seams and concealed mounting of upholstery to ensure that rigorous infection control standards can be met.



### FEATURES

- Frame:** Folding Steel Frame
- Legrest:** Swing-away, Removable (Elevating optional accessory)
- Footrest:** Height Adjustable
- Armrest:** Swing-back, Removable
- Wheels:** Quick Release, Solid 24" Tyres
- Castors:** 8", Height Adjustable
- Brakes:** Push-to-lock
- Seat:** Fixed, Padded, Fire Retardant Vinyl
- Backrest:** Fixed, Padded, Fire Retardant Vinyl
- Upholstery:** Hospital Grade Fire Retardant Vinyl
- Cushion:** Optional Accessory
- Weight:** From 17.3kg
- Security:** Simple Frame Fix Mod to Stop Chair Being Folded (Available as option on request)

### INFECTION CONTROL FOCUS

- Durable hospital vinyl that is easy to wipe clean
- Fully welded seams to inhibit bacterial growth
- Concealed mounting of upholstery to prevent fluid ingress

### ASSET SECURITY

The centre cross-brace of the ASSIST 2 WARD can be customised to fix the frame for Hospital Asset Security.

### DURABLE TRANSPORT SOLUTION

The ASSIST 2 WARD Vinyl is a versatile transport wheelchair. Quick release wheels with solid, maintenance-free tyres provide on-call reliability and are suitable for use in common areas, corridors, wards, bathrooms and outdoors.

| SEAT WIDTH   | CODE                         |
|--------------|------------------------------|
| 350 mm (14") | MWS449340                    |
| 400 mm (16") | MWS449350                    |
| 450 mm (18") | MWS449360                    |
| 500 mm (20") | MWS449370                    |
| 570 mm (22") | MWS449380 (HEAVY DUTY Model) |
| 610 mm (24") | MWS449390 (HEAVY DUTY Model) |



- DVA Contracted
- AS / NZS Approved
- Assist 2 is registered in the ARTG, AUST R ARTG 291670

\*For Detailed Features, Specifications and Accessories see pages 14 - 20





# aspire TRANSIT 2 *Transporter*

The Aspire TRANSIT 2 wheelchair is a versatile and robust transport wheelchair that is propelled by an attendant or carer. The Aspire TRANSIT 2 is a reliable and comfortable solution, with various accessories available to suit the needs of individuals and carers in the Community, Hospital or Aged Care environments.



## FEATURES

- Frame:** Folding Steel Frame
- Legrest:** Swing-away, Removable, (Elevating optional accessory)
- Footrest:** Height Adjustable
- Armrest:** Swing-away, Removable
- Wheels:** Quick Release, Solid 12" Tyres
- Castors:** 8", Height Adjustable
- Brakes:** Attendant Push-to-lock
- Seat:** Fixed, Light Padding
- Backrest:** Fixed, Light Padding
- Upholstery:** Dacron Fire Retardant Fabric
- Cushion:** Optional Accessory
- Weight:** From 16.4kg

### SWING-AWAY ARMRESTS

The padded armrests are swing-away and removable to facilitate the user when transferring in and out of the chair.

### DURABLE TRANSPORT SOLUTION

The Aspire TRANSIT 2 is a versatile transport wheelchair, with rear 12 inch puncture-proof, transit wheels to allow an attendant or carer to easily navigate a client to their destination.

### FOLDING DESIGN

The centre cross-brace design allows for the Aspire TRANSIT 2 to be folded up for unoccupied transport or storage within a facility, hire or community environment.

| SEAT WIDTH   | CODE      |
|--------------|-----------|
| 400 mm (16") | MWS449410 |
| 450 mm (18") | MWS449420 |
| 500 mm (20") | MWS449430 |



- DVA Contracted
- AS / NZS Approved
- Transit is registered in the ARTG, AUST R ARTG 291670

\*For Detailed Features, Specifications and Accessories see pages 14 - 20



# aspire LITE TRANSIT

The Aspire LITE TRANSIT is an lightweight wheelchair ideal for carer assisted transport. The compact lightweight frame makes it easy to transfer in and out of the car. Attendant brakes and 12 inch rear wheels assist the carer in negotiating indoor and outdoor terrain smoothly and safely. While the height adjustable armrests allow the user close access to tables or quick adjustment for comfort.

# aspire LITE (ULTRALITE)


The Aspire LITE is an 'ultra lightweight' wheelchair that is ideal for occasional use. The Aspire LITE is designed with the carer in mind. The compact, lightweight frame makes it easy to transfer in and out of a car. The push button, height adjustable armrests make it versatile, allowing the user to be positioned at a table and quickly adjusted for comfort.

Attendant operated brakes



## FEATURES

- Frame:** Folding Aluminium Frame
- Legrest:** Swing-away & Removable
- Armrest:** Height Adjustable
- Wheels:** Solid 12" Tyres
- Castors:** 6" Height
- Brakes:** Attendant Brakes & Push-to-lock Brakes
- Upholstery:** Padded Dacron Fabric
- Weight:** Chair Weight 11.6kg



### SAFETY

Safety lap belt & attendant brakes

### LIGHTWEIGHT


Reduced manual handling effort.

### TRANSPORTABLE

Easily folded due to its centre cross brace design. The attendant handles can also be folded down, taking up minimal car space.

## FEATURES

- Frame:** Folding Aluminium Frame
- Legrest:** Swing-away & Removable
- Armrest:** Height Adjustable
- Wheels:** Solid 8" Tyres
- Castors:** 6" Height
- Brakes:** Push-to-lock
- Upholstery:** Padded Dacron Fabric
- Weight:** Chair Weight 9.5kg



### SAFETY & STORAGE

Safety lap belt & rear storage pocket

### ULTRA LIGHTWEIGHT

At 9.5kg, allows for minimal manual handling.

### TRANSPORTABLE

Easily folded due to its centre cross brace design. The attendant handles can also be folded down, taking up minimal car space.

| CHAIR        | SEAT WIDTH   | CODE      |
|--------------|--------------|-----------|
| TRANSIT LITE | 460 mm (18") | MWS442301 |
| LITE         | 460 mm (18") | MWS442300 |






- DVA Contracted
- AS / NZS Approved

- Lite Transit is registered in the ARTG, AUST R ARTG 229423
- Lite is registered in the ARTG, AUST R ARTG 229423









































\*For Detailed Features, Specifications and Accessories see pages 14 - 20



# aspire FEATURES MATRIX

| DESCRIPTION                  | SUITS   |   |   |   |   |   |   |   |   |
|------------------------------|---|---|---|---|---|---|---|---|---|
|                              |  |  |  |  |  |  |  |  |  |
| Aluminium                    | ●   | ●   |   |   |   |   |   | ●   | ●   |
| Steel                        |   |   | ●   | ●   | ●   | ●   | ●   |   |   |
| Folding                      | ●   | ●   |   |   |   | ●   | ●   | ●   | ●   |
| <b>SEAT</b>                  |   |   |   |   |   |   |   |   |   |
| Depth adjustable             | ●   | ●   | ●   | ●   | ●   |   |   |   |   |
| Width adjustable             |   |   | ●   | ●   | ●   |   |   |   |   |
| Cushion included             | ●   | ●   | ●   | ●   | ●   |   |   |   |   |
| <b>WHEELS</b>                |   |   |   |   |   |   |   |   |   |
| Quick release                | ●   | ●   | ●   | ●   | ●   | ●   | ●   |   |   |
| Solid tyres                  | ●   | ●   | ●   | ●   | ●   | ●   | ●   | ●   | ●   |
| 24" wheels                   | ●   |   |   | ●   | ●   | ●   |   |   |   |
| 20" wheels                   |   | ●   | ●   |   |   |   |   |   |   |
| 12" wheels                   |   |   |   |   |   |   | ●   | ●   |   |
| 8" wheels                    |   |   |   |   |   |   |   |   | ●   |
| <b>LEGRESTS</b>              |   |   |   |   |   |   |   |   |   |
| Swing-away                   | ●   | ●   | ●   | ●   | ●   | ●   | ●   | ●   | ●   |
| Removable                    | ●   | ●   | ●   | ●   | ●   | ●   | ●   | ●   | ●   |
| Padded                       |   |   | ●   | ●   | ●   |   |   |   |   |
| Elevating                    |   |   | ●   | ●   | ●   |   |   |   |   |
| <b>ARMRESTS</b>              |   |   |   |   |   |   |   |   |   |
| Swing-away                   | ●   | ●   |   |   |   | ●   | ●   |   |   |
| Removable                    | ●   | ●   | ●   | ●   | ●   | ●   | ●   |   |   |
| Height adjustable            |   |   | ●   | ●   | ●   |   |   | ●   | ●   |
| Depth adjustable             |   |   | ●   | ●   | ●   |   |   |   |   |
| <b>BACKREST</b>              |   |   |   |   |   |   |   |   |   |
| Height adjustable back canes | ●   | ●   | ●   | ●   | ●   |   |   |   |   |
| Tension adjustable backrest  | ●   | ●   | ●   | ●   | ●   |   |   |   |   |
| <b>BRAKES</b>                |   |   |   |   |   |   |   |   |   |
| Drum Brakes                  |   |   | ●   | ●   | ●   |   |   |   |   |
| Attendant Brakes             |   |   | ●   | ●   | ●   |   |   | ●   |   |
| <b>OTHER FEATURES</b>        |   |   |   |   |   |   |   |   |   |
| Self-propelled               | ●   | ●   | ●   | ●   | ●   | ●   |   |   |   |
| Attendant-propelled only     |   |   |   |   |   |   | ●   | ●   | ●   |
| Tilts                        |   |   | ●   | ●   | ●   |   |   |   |   |
| Reclines                     |   |   | ●   | ●   | ●   |   |   |   |   |
| Crash tested                 | ●   | ●   | ●   | ●   | ●   |   |   |   |   |

# TECHNICAL SPECIFICATIONS

| CODE                | SEAT WIDTH  | OVERALL WIDTH   | SEAT DEPTH  | SEAT HEIGHT   | BACKREST HEIGHT   | ARMREST HEIGHT  | MINIMUM CHAIR WEIGHT  | S.W.L   |
|---------------------|---|---|---|---|---|---|---|---|
| <b>EVOKE 2</b>      |    |    |    |    |    |    |    |    |
| MWS449500           | 350 mm (14")  | 560 mm  | 400 - 475 mm  | 440 - 480 mm  | 430 - 490 mm  | 205 - 225 mm  | From 14.8 kg  | 140 kg  |
| MWS449510           | 400 mm (16")  | 610 mm  | 400 - 475 mm  | 440 - 480 mm  | 430 - 490 mm  | 205 - 225 mm  | From 14.9 kg  | 140 kg  |
| MWS449520           | 450 mm (18")  | 660 mm  | 400 - 475 mm  | 440 - 480 mm  | 430 - 490 mm  | 205 - 225 mm  | From 15.0 kg  | 140 kg  |
| MWS449530           | 500 mm (20")  | 710 mm  | 400 - 475 mm  | 440 - 480 mm  | 430 - 490 mm  | 205 - 225 mm  | From 15.1 kg  | 140 kg  |
| MWS449540 (HD)      | 570 mm (22")  | 780 mm  | 400 - 475 mm  | 440 - 480 mm  | 430 - 490 mm  | 205 - 225 mm  | From 16.0 kg  | 180 kg  |
| MWS449550 (HD)      | 610 mm (24")  | 820 mm  | 400 - 475 mm  | 440 - 480 mm  | 430 - 490 mm  | 205 - 225 mm  | From 16.2 kg  | 180 kg  |
| <b>EVOKE 2 JNR</b>  |   |   |   |   |   |   |   |   |
| MWS449560           | 300 mm (12")  | 510 mm  | 300 - 375 mm  | 360 - 410 mm  | 430 - 490 mm  | 205 - 225 mm  | 14 kg   | 140 kg  |
| <b>REHAB RX JNR</b> |  |  |  |  |  |  |  |  |
| MWS449630           | 320 - 370 mm (13" - 15")  | 600 mm  | 440 - 490 mm  | Front = 410 - 440 mm<br>Rear = 400 - 475 mm   | 460 - 710 mm  | 310 - 460 mm  | 39.5 kg   | 180 kg  |
| <b>REHAB RX</b>     |  |  |  |  |  |  |  |  |
| MWS449710           | 410 - 460 mm (16" - 18")  | 690 mm  | 440 - 530 mm  | Front = 410 - 440 mm<br>Rear = 400 - 475 mm   | 460 - 710 mm  | 310 - 460 mm  | 41 kg   | 180 kg  |
| MWS449720           | 460 - 510 mm (18" - 20")  | 740 mm  | 440 - 530 mm  | Front = 410 - 440 mm<br>Rear = 400 - 475 mm   | 460 - 710 mm  | 310 - 460 mm  | 43 kg   | 180 kg  |
| MWS449740           | 510 - 560 mm (20" - 22")  | 790 mm  | 470 - 560 mm  | Front = 410 - 440 mm<br>Rear = 400 - 475 mm   | 460 - 710 mm  | 310 - 460 mm  | 47.2 kg   | 180 kg  |
| <b>REHAB RS</b>     |  |  |  |  |  |  |  |  |
| MWS449600           | 410 - 460 mm (16" - 18")  | 690 mm  | 440 - 530 mm  | Front = 410 - 440 mm<br>Rear = 400 - 475 mm   | 460 - 710 mm  | 310 - 460 mm  | 40.7 kg   | 180 kg  |
| MWS449610           | 460 - 510 mm (18" - 20")  | 740 mm  | 440 - 530 mm  | Front = 410 - 440 mm<br>Rear = 400 - 475 mm   | 460 - 710 mm  | 310 - 460 mm  | 42.5 kg   | 180 kg  |
| MWS449620           | 510 - 560 mm (20" - 22")  | 790 mm  | 470 - 560 mm  | Front = 410 - 440 mm<br>Rear = 400 - 475 mm   | 460 - 710 mm  | 310 - 460 mm  | 46.7 kg   | 180 kg  |

Note: Seat height for REHAB RS, RX, RX JNR, EVOKE 2 & EVOKE 2 JNR is without seat cushion. Standard seat cushion height is 100 mm.




# TECHNICAL SPECIFICATIONS

| CODE                        | SEAT WIDTH   | OVERALL WIDTH | SEAT DEPTH | SEAT HEIGHT  | BACKREST HEIGHT | ARMREST HEIGHT | MINIMUM CHAIR WEIGHT | S.W.L  |
|-----------------------------|--------------|---------------|------------|--------------|-----------------|----------------|----------------------|--------|
| <b>ASSIST 2</b>             |              |               |            |              |                 |                |                      |        |
| MWS449300                   | 350 mm (14") | 570 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 17.3 kg              | 140 kg |
| MWS449310                   | 400 mm (16") | 620 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 17.5 kg              | 140 kg |
| MWS449320                   | 450 mm (18") | 670 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 17.7 kg              | 140 kg |
| MWS449330                   | 500 mm (20") | 720 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 17.9 kg              | 140 kg |
| MWS449340 (DELUXE VINYL)    | 350 mm (14") | 570 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 17.4 kg              | 140 kg |
| MWS449350 (DELUXE VINYL)    | 400 mm (16") | 620 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 17.6 kg              | 140 kg |
| MWS449360 (DELUXE VINYL)    | 450 mm (18") | 670 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 17.8 kg              | 140 kg |
| MWS449370 (DELUXE VINYL)    | 500 mm (20") | 720 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 18 kg                | 140 kg |
| MWS449380 (HD DELUXE VINYL) | 570 mm (22") | 790 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 18.9 kg              | 180 kg |
| MWS449390 (HD DELUXE VINYL) | 610 mm (24") | 830 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 19.2 kg              | 180 kg |
| <b>TRANSIT 2</b>            |              |               |            |              |                 |                |                      |        |
| MWS449410                   | 400 mm (16") | 540 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 16.4 kg              | 140 kg |
| MWS449420                   | 450 mm (18") | 590 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 16.6 kg              | 140 kg |
| MWS449430                   | 500 mm (20") | 640 mm        | 400 mm     | 460 - 500 mm | 440 mm          | 210 mm         | 16.8 kg              | 140 kg |
| <b>LITE TRANSIT</b>         |              |               |            |              |                 |                |                      |        |
| MWS442301                   | 460 mm (18") | 600 mm        | 400 mm     | 460 mm       | 465 mm          | 235 mm         | 11.6 kg              | 120 kg |
| <b>LITE</b>                 |              |               |            |              |                 |                |                      |        |
| MWS442300                   | 460 mm (18") | 550 mm        | 400 mm     | 460 mm       | 465 mm          | 235 mm         | 9.5 kg               | 120 kg |

# ACCESSORIES



**OXYGEN BOTTLE HOLDER**



**BASE FRAME EXTENSION KITS**



**STUMP SUPPORT**



**ELEVATING LEGRESTS**



**OXYGEN BOTTLE BAG**



**DELUXE HEADREST**




**ANTI-TIP BARS**



**MEAL TRAY**



**CONTOURED PADDED OVERLAY**



**DEPTH & HEIGHT ADJUSTABLE ARMRESTS**



**CALF STRAP**



**GUTTER ARMRESTS**



**SAFETY LAP BELT**




**BRAKE EXTENSION LEVERS**



**LATERAL CHEST SUPPORT**



**THERAPIST-FRIENDLY, TOOL-FREE ADJUSTMENT KIT**



**CAMBER KIT**



**EXTENDED BACK CANES**













✓ Extends up to 50mm to facilitate easy movement for taller carers



**DRUM BRAKE KITS**






















# ACCESSORIES MATRIX

| CODE                         | DESCRIPTION  | SUITS   |   |   |  |  |  |   |   |
|------------------------------|--|---|---|---|--|--|--|---|---|
|                              |  |  Evoke 2 |  Evoke 2 JNR |  Rehab RX JNR |  Rehab RX |  Rehab RS |  Assist 2 |  Transit 2 |   |
| <b>ELEVATING LEGRESTS</b>    |  |   |   |   |  |  |  |   |   |
| WCA848100                    | Elevating Legrest - Left - 300/320/350/400/410mm       |          | ●   | ●   | ○  | ○  | ○  | ●   | ● |
| WCA848110                    | Elevating Legrest - Right - 300/320/350/400/410mm      |   | ●   | ●   | ○  | ○  | ○  | ●   | ● |
| WCA848120                    | Elevating Legrest - Left - 450/460/500/510mm           |   | ●   |   |  | ○  | ○  | ●   | ● |
| WCA848130                    | Elevating Legrest - Right - 450/460/500/510mm          |   | ●   |   |  | ○  | ○  | ●   | ● |
| WCA848140                    | Elevating Legrest - Left - 570/610mm                   |   | ●   |   |  |  |  | ●   |   |
| WCA848150                    | Elevating Legrest - Right - 570/610mm                  |   | ●   |   |  |  |  | ●   |   |
| <b>STUMP SUPPORTS</b>        |  |   |   |   |  |  |  |   |   |
| WCA848220                    | Stump Support - Left - Silver - 300/320/350/400/450mm  |   | ●   | ●   | ●  | ●  | ●  | ●   | ● |
| WCA848230                    | Stump Support - Right - Silver - 300/320/350/400/450mm |   | ●   | ●   | ●  | ●  | ●  | ●   | ● |
| WCA848240                    | Stump Support - Left - Silver - 500/550/570/610mm      |         | ●   |   |  | ●  | ●  | ●   | ● |
| WCA848250                    | Stump Support - Right - Silver - 500/550/570/610mm     |   | ●   |   |  | ●  | ●  | ●   | ● |
| WCA848260                    | Stump Support - Extension Bracket - Silver             |   | ●   | ●   |  |  |  | ●   | ● |
| <b>OXYGEN BOTTLE HOLDERS</b> |  |   |   |   |  |  |  |   |   |
| WCA848290                    | Oxygen Bottle Holder                                   |        | ●   | ●   |  |  |  | ●   | ● |
| WAA695600                    | Oxygen Bottle Bag                                      |   |   |   | ●  | ●  | ●  |   |   |
| <b>BRAKE EXTENSIONS</b>      |  |   |   |   |  |  |  |   |   |
| WCA848310                    | Brake Extension Lever - Left                           |        | ●   | ●   |  |  |  | ●   | ● |
| WCA848320                    | Brake Extension Lever - Right                          |   | ●   | ●   |  |  |  | ●   | ● |
| <b>LATERAL SUPPORTS</b>      |  |   |   |   |  |  |  |   |   |
| WCA848430                    | Lateral Chest Support - Left                           |        | ●   | ●   |  |  |  |   |   |
| WCA848440                    | Lateral Chest Support - Right                          |   | ●   | ●   |  |  |  |   |   |
| WCA848450                    | Lateral Chest Support - Left                           |   |   |   |  | ●  | ●  |   |   |
| WCA848460                    | Lateral Chest Support - Right                          |   |   |   |  | ●  | ●  |   |   |

○ - Standard Feature Included

# ACCESSORIES MATRIX

| CODE  | DESCRIPTION                                 | SUITS   |   |  |  |  |  |   |   |
|---|---|---|---|--|--|--|--|---|---|
|   |   |  Evoke 2 |  Evoke 2 JNR |  Rehab RX JNR |  Rehab RX |  Rehab RS |  Assist 2 |  Transit 2 |   |
| <b>CONTOURED PADDED OVERLAYS</b>              |   |   |   |  |  |  |  |   |   |
| WCA848330                                     | Contoured Padded Overlay - 350mm Wide       |          | ●   |  |  |  |  | ●   |   |
| WCA848340                                     | Contoured Padded Overlay - 400mm Wide       |   | ●   |  |  |  |  | ●   | ● |
| WCA848350                                     | Contoured Padded Overlay - 450mm Wide       |   | ●   |  |  |  |  | ●   | ● |
| WCA848360                                     | Contoured Padded Overlay - 500mm Wide       |   | ●   |  |  |  |  | ●   | ● |
| WCA848370                                     | Contoured Padded Overlay - 570mm Wide       |   | ●   |  |  |  |  | ●   |   |
| WCA848380                                     | Contoured Padded Overlay - 610mm Wide       |   | ●   |  |  |  |  | ●   |   |
| <b>DEPTH &amp; HEIGHT ADJUSTABLE ARMRESTS</b> |   |   |   |  |  |  |  |   |   |
| WCA848390                                     | Depth & Height Adjustable Armrest - Left    |          | ●   |  |  |  |  |   |   |
| WCA848400                                     | Depth & Height Adjustable Armrest - Right   |   | ●   |  |  |  |  |   |   |
| <b>GUTTER ARMRESTS *</b>                      |   |   |   |  |  |  |  |   |   |
| WCA848410                                     | Gutter Armrest Pad - Left                   |         | ●   |  |  |  |  |   |   |
| WCA848420                                     | Gutter Armrest Pad - Right                  |   | ●   |  |  |  |  |   |   |
| <b>DRUM BRAKES</b>                            |   |   |   |  |  |  |  |   |   |
| WCA848510                                     | Rear Wheels w/Drum Brakes Kit - 16in        |        |   | ●  | ●  | ●  | ●  |   |   |
| WCA848520                                     | Rear Wheels w/Drum Brakes Kit - 20in        |   |   | ●  | ○  | ●  | ●  |   |   |
| WCA848500                                     | Rear Wheels w/Drum Brakes Kit - 24in        |   | ●   |  |  | ○  | ○  |   |   |
| <b>DEPTH EXTENSIONS</b>                       |   |   |   |  |  |  |  |   |   |
| WCA848530                                     | Base Frame Extension Kit - 50mm - Black     |        |   |  |  | ●  | ●  |   |   |
| WCA848540                                     | Base Frame Extension Kit - 100mm - Black    |   |   |  |  | ●  | ●  |   |   |
| <b>OTHER</b>                                  |   |   |   |  |  |  |  |   |   |
| WCA848550                                     | Therapist-Friendly Tool-Free Adjustment Kit |        |   |  | ●  | ●  | ●  |   |   |
| WCA848560                                     | Meal Tray - 320mm to 410mm                  |   |   |  | ●  | ●  | ●  |   |   |
| WCA848570                                     | Meal Tray - 460mm to 510mm                  |        |   |  |  | ●  | ●  |   |   |
| WCA848270                                     | Anti-Tip Bars                               |        | ●   | ●  | ○  | ○  | ○  | ●   | ● |
| WCA848280                                     | IV Pole                                     |        | ●   | ●  | ●  | ●  | ●  | ●   | ● |
| WCA848300                                     | Safety Lap Belt - Metal Seatbelt Buckle     |        | ●   | ●  | ●  | ●  | ●  | ●   | ● |
| WCA848470                                     | Extended Back Cane - Pair - 19/21in         |        | ●   | ●  |  |  |  |   |   |
| WCA848480                                     | Headrest Assembly - Deluxe Style            |        | ●   | ●  |  |  |  |   |   |
| WCA848580                                     | Calf Strap                                  |        | ●   | ●  | ●  | ●  | ●  | ●   | ● |
| WCA848490                                     | Camber Kit                                  |        | ●   | ●  |  |  |  |   |   |
| AAL848590                                     | Security Mod - ASSIST 2 WARD Only           |   |   |  |  |  |  | ●   |   |

○ - Standard Feature Included \*Note: Side transfers are not possible when gutter armrests are attached



CRUTCHES, FRAMES & STICKS



SCOOTERS



OVERBED TABLES



BED STICKS & POLES



RAMPS



AIR MATTRESSES & FOAM MATTRESSES



COMMODES, URINALS & BED PANS



OVER TOILET AIDS



SHOWER STOOLS & CHAIRS



RAISED TOILET SEATS



SHOWER COMMODES



BATH BOARDS & BENCHES



SEAT WALKERS



POWER WHEELCHAIRS



PRESSURE CUSHIONS



LIFT & RECLINE CHAIRS



Distributed by:

ASBR20.69 240720

