



# Exciting New Additions to DVA

## Our Latest Wheelchairs & Accessories



### aspire Evoke 2

- Lightweight
- Foldable
- Highly Adjustable
- Cushion Included

 RAP # AP17

Code	Seat Width	SWL
MWS449500	350 mm (14")	140 kg
MWS449510	400 mm (16")	140 kg
MWS449520	450 mm (18")	140 kg
MWS449530	500 mm (20")	140 kg
MWS449540 (HD)	570 mm (22")	180 kg
MWS449550 (HD)	610 mm (24")	180 kg



### aspire Rehab RX

- Tilt-in-Space Design
- Extensive Adjustability
- Pressure Care Surfaces
- Increased Support
- Articulating Elevating Legrests

 RAP # AP17

Code	Seat Width	SWL
MWS449710	410 - 460 mm (16" - 18")	180 kg
MWS449720	460 - 510 mm (18" - 20")	180 kg
MWS449740	510 - 560 mm (20" - 22")	180 kg



### aspire Rehab RS

- Tilt-in-Space Design
- Advanced Comfort
- Increased Support
- Highly Adjustable
- Supportive & Comfortable

 RAP # AP17

Code	Seat Width	SWL
MWS449600	410mm (16")	180 kg
MWS449610	460mm (18")	180 kg
MWS449620	510mm (20")	180 kg



### aspire Assist 2

- Robust
- Foldable
- Suitable for a variety of environments

 RAP # AP17

Code	Seat Width	SWL
MWS449300	350mm (14")	140 kg
MWS449310	400mm (16")	140 kg
MWS449320	450mm (18")	140 kg
MWS449330	500mm (20")	140 kg
MWS449340	350mm (14")	140 kg
MWS449350	400mm (16")	140 kg
MWS449360	450mm (18")	140 kg
MWS449370	500mm (20")	140 kg
MWS449380	570mm (22")	180 kg
MWS449390	610mm (24")	180 kg














### aspire Transit 2

- Robust & Reliable
- Folding
- Swing-Away Armrests
- Padded Nylon Upholstery


















 ERAP # AP17

Code	Seat Width	SWL
MWS449410	400 mm (16")	140 kg
MWS449420	450 mm (18")	140 kg
MWS449430	500 mm (20")	140 kg

CODE	DESCRIPTION	SUITS					
		 Evoke 2	 Rehab RX	 Rehab RS	 Assist 2	 Transit 2	
<b>ELEVATING LEGRESTS</b>							
WCA848100	Elevating Legrest - Left - 300/320/350/400/410mm		●	●	○	●	●
WCA848110	Elevating Legrest - Right - 300/320/350/400/410mm		●	●	○	●	●
WCA848120	Elevating Legrest - Left - 450/460/500/510mm		●	○	●	●	
WCA848130	Elevating Legrest - Right - 450/460/500/510mm		●	○	●	●	
WCA848140	Elevating Legrest - Left - 570/610mm		●		●		
WCA848150	Elevating Legrest - Right - 570/610mm		●		●		
<b>ADVANCED ARTICULATING ELEVATING LEGRESTS</b>							
WCA848160	Elevating Legrest - Articulating - Left - 300/320/350/400/410mm		○	●	●	●	
WCA848170	Elevating Legrest - Articulating - Right - 300/320/350/400/410mm		○	●	●	●	
WCA848180	Elevating Legrest - Articulating - Left - 450/460/500/510mm		○	●	●	●	
WCA848190	Elevating Legrest - Articulating - Right - 450/460/500/510mm		○	●	●	●	
WCA848200	Elevating Legrest - Articulating - Left - 570/610mm		●			●	
WCA848210	Elevating Legrest - Articulating - Right - 570/610mm		●			●	
<b>STUMP SUPPORTS</b>							
WCA848220	Stump Support - Left - Silver - 300/320/350/400/450mm		●	●	●	●	
WCA848230	Stump Support - Right - Silver - 300/320/350/400/450mm		●	●	●	●	
WCA848240	Stump Support - Left - Silver - 500/550/570/610mm		●	●	●	●	
WCA848250	Stump Support - Right - Silver - 500/550/570/610mm		●	●	●	●	
WCA848260	Stump Support - Extension Bracket - Silver		●			●	●
<b>OXYGEN BOTTLE HOLDERS</b>							
WCA848290	Oxygen Bottle Holder		●			●	●
WAA695600	Oxygen Bottle Bag		●	●			
<b>BRAKE EXTENSIONS</b>							
WCA848310	Brake Extension Lever - Left		●			●	●
WCA848320	Brake Extension Lever - Right		●			●	●
<b>LATERAL SUPPORTS</b>							
WCA848430	Lateral Chest Support Assembly - Left		●				
WCA848440	Lateral Chest Support Assembly - Right		●				

○ - Standard Feature Included

 RAP # AP14

CODE	DESCRIPTION	SUITS					
		 Evoke 2	 Rehab RX	 Rehab RS	 Assist 2	 Transit 2	
<b>CONTOURED PADDED OVERLAYS</b>							
WCA848340	Contoured Padded Overlay - 400mm Wide		●				
WCA848350	Contoured Padded Overlay - 450mm Wide		●				
WCA848360	Contoured Padded Overlay - 500mm Wide		●				
WCA848370	Contoured Padded Overlay - 570mm Wide		●				
WCA848380	Contoured Padded Overlay - 610mm Wide		●				
<b>DEPTH &amp; HEIGHT ADJUSTABLE ARMRESTS</b>							
WCA848390	Depth & Height Adjustable Armrest - Left		●				
WCA848400	Depth & Height Adjustable Armrest - Right		●				
<b>GUTTER ARMRESTS</b>							
WCA848410	Gutter Armrest Pad - Left		●				
WCA848420	Gutter Armrest Pad - Right		●				
<b>DRUM BRAKES</b>							
WCA848510	Rear Wheels w/Drum Brakes Kit - 16in			●	●		
WCA848520	Rear Wheels w/Drum Brakes Kit - 20in			●	●		
WCA848500	Rear Wheels w/Drum Brakes Kit - 24in		●	○	○		
<b>DEPTH EXTENSIONS</b>							
WCA848530	Base Frame Extension Kit - 50mm - Black			●	●		
WCA848540	Base Frame Extension Kit - 100mm - Black			●	●		
<b>OTHER</b>							
WCA848560	Meal Tray - 320mm to 410mm			●	●		
WCA848570	Meal Tray - 460mm to 510mm			●	●		
WCA848270	Anti-Tip Bars		●	○	○	●	●
WCA848280	IV Pole		●	●	●	●	●
WCA848300	Safety Lap Belt - Metal Seatbelt Buckle		●	●	●	●	●
WCA848470	Extended Back Cane - Pair - 19/21in		●				
WCA848480	Headrest Assembly - Deluxe Style		●				
WCA848580	Calf Strap		●	●	●	●	●

○ - Standard Feature Included

 RAP # AP14

## Our Latest Scooter Models



### **Pride** Pathrider 130XL Pursuit - 4 Wheel Red

- Seat post suspension for a smoother ride
- Front basket and rearview mirror standard
- Easily accessible tie down points (for transport of unoccupied scooter)
- Full lighting package that includes directional signals and angle adjustable, dual bulb lower headlight

Code	Total Length	Total Width	Maximum Speed	Total Range	SWL
SCT670571	1359mm	635mm	12.4km/h	24.9km	158kg



### **Pride** Victory 10 LX - 4 Wheel Red *Includes Rear Bag and Cane Holder*

- Sleek, modern, modular design for easy serviceability
- Full LED lighting package that includes curb and rear lights and directional signals
- Storage compartment below tiller
- Feather-touch disassembly permits simple frame separation with only one hand

Code	Total Length	Total Width	Maximum Speed	Total Range	SWL
SCT670640	1194mm	565mm	9km/h	26km	181kg

